



1N4933G THRU 1N4937G

1.0 AMP. Glass Passivated Fast Recovery Rectifiers



Voltage Range
50 to 600 Volts
Current
1.0 Ampere


Features

- ✧ Low forward voltage drop
- ✧ High current capability
- ✧ High reliability
- ✧ High surge current capability

Mechanical Data

- ✧ Cases: Molded plastic DO-41
- ✧ Epoxy: UL 94V-O rate flame retardant
- ✧ Lead: Axial leads, solderable per MIL-STD-202, Method 208 guaranteed
- ✧ Polarity: Color band denotes cathode end
- ✧ High temperature soldering guaranteed: 250°C/10 seconds/.375", (9.5mm) lead lengths at 5 lbs., (2.3kg) tension
- ✧ Weight: 0.34gram

DO-41



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	1N4933G	1N4934G	1N4935G	1N4936G	1N4937G	Units
Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	V
Maximum RMS Voltage	35	70	140	280	420	V
Maximum DC Blocking Voltage	50	100	200	400	600	V
Maximum Average Forward Rectified Current .375 (9.5mm) Lead Length @ T _A = 75°C	1.0					A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	30					A
Maximum Instantaneous Forward Voltage @ 1.0A	1.2					V
Maximum DC Reverse Current @ T _A =25°C at Rated DC Blocking Voltage @ T _A =125°C	5.0 100					µA µA
Maximum Reverse Recovery Time (Note 1)	150					nS
Typical Junction Capacitance (Note 2)	15					pF
Typical Thermal Resistance (Note 3) RθJA	55					°C/W
Operating Temperature Range T _J	-65 to +150					°C
Storage Temperature Range T _{STG}	-65 to +150					°C

Notes: 1. Reverse Recovery Test Conditions: I_F=0.5A, I_R=1.0A, I_{RR}=0.25A

2. Measured at 1 MHz and Applied Reverse Voltage of 4.0 V D.C.

3. Thermal Resistance from Junction to Ambient at 0.375"(9.5mm) Lead Length, P.C.B. Mounted

RATINGS AND CHARACTERISTIC CURVES (1N4933G THRU 1N4937G)

FIG.1- REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM





FIG.2- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.3- MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG.4- TYPICAL JUNCTION CAPACITANCE




FIG.5- TYPICAL FORWARD CHARACTERISTICS




FIG.6- TYPICAL REVERSE CHARACTERISTICS

