

FCI CONFIDENTIAL

List of "HFW__R-1/2STE9LF" customer document

DOCUMENT NO.	LIST
10101162(SHEET1)	DOCUMENT LIST
10101162(SHEET2)	CAT.NO.TABLE FOR 1mm SPACING SMT CONNECTOR (HFW__R-1/2ST__LF)
10101162(SHEET3)	1mm SPACING SMT CONNECTOR (HFW__R-1ST_LF)
10101162(SHEET4)	1mm SPACING SMT CONNECTOR (HFW__R-2ST_LF)
10101162(SHEET5)	CAT.NO.TABLE FOR PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (HFW__R-1/2STE9LF)
10101162(SHEET6)	PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (HFW__R-1STE9LF)
10101162(SHEET7)	PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (HFW__R-2STE9LF)
10101162(SHEET8)	RECOMMENDED CABLE (FPC) (HFW__R-1/2ST__)
10101162(SHEET9)	RECOMMENDED CABLE (FFC) (HFW__R-1/2ST__)
SC-HFWR02	PRODUCT SPECIFICATION
BJM HFWR101	HANDLING PROCEDURES

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI.
Copyright FCI.

mat'l. code				surface ISO 1302 ☒				tolerance ISO 406 ISO 1101				projection 				product family 58NF				CODE JP																	
ltr		ecn no		dr		date		tolerances unless otherwise specified				mm 				title 1mm SPACING SMT CONNECTOR DOCUMENT LIST (Cat. No. : HFW__R-1/2STE9LF)																					
A		S09-0139		DGOH		09-05-06		angles linear																													
												scale				dwg no 10101162 sheet 1 of 9 size A4																					
												FCI																									
								dr				DENNIS GOH				09-05-06				type Product Customer Drawing																	
								engr				DENNIS GOH				09-05-06																					
								chr				DENNIS GOH				09-05-06				Rev. A																	
								appd				JOEY NG				09-05-06																					
sheet index		revision sheet		A 1		A 2		A 3		A 4		A 5		A 6		A 7		A 8		A 9																	

CAT. NO. & DIMENSIONS

(NOTE3)	NO. OF CONTACTS (n)	CAT. NO.	DIMENSIONS (NOTE2)		
			A ± 0.2	B ± 0.2	C ± 0.1
	4	HFW4R-1/2ST__LF	6.6	3	5.14
	5	HFW5R-1/2ST__LF	7.6	4	6.14
	6	HFW6R-1/2ST__LF	8.6	5	7.14
	7	HFW7R-1/2ST__LF	9.6	6	8.14
	8	HFW8R-1/2ST__LF	10.6	7	9.14
	9	HFW9R-1/2ST__LF	11.6	8	10.14
	10	HFW10R-1/2ST__LF	12.6	9	11.14
	11	HFW11R-1/2ST__LF	13.6	10	12.14
	12	HFW12R-1/2ST__LF	14.6	11	13.14
	13	HFW13R-1/2ST__LF	15.6	12	14.14
	14	HFW14R-1/2ST__LF	16.6	13	15.14
	15	HFW15R-1/2ST__LF	17.6	14	16.14
	16	HFW16R-1/2ST__LF	18.6	15	17.14
	17	HFW17R-1/2ST__LF	19.6	16	18.14
	18	HFW18R-1/2ST__LF	20.6	17	19.14
	19	HFW19R-1/2ST__LF	21.6	18	20.14
	20	HFW20R-1/2ST__LF	22.6	19	21.14
	21	HFW21R-1/2ST__LF	23.6	20	22.14
	22	HFW22R-1/2ST__LF	24.6	21	23.14
	23	HFW23R-1/2ST__LF	25.6	22	24.14
	24	HFW24R-1/2ST__LF	26.6	23	25.14
	25	HFW25R-1/2ST__LF	27.6	24	26.14
	26	HFW26R-1/2ST__LF	28.6	25	27.14
	27	HFW27R-1/2ST__LF	29.6	26	28.14
*	28	HFW28R-1/2ST__LF	30.6	27	29.14
*	29	HFW29R-1/2ST__LF	31.6	28	30.14
	30	HFW30R-1/2ST__LF	32.6	29	31.14

CAT. NO. HFW (n) R - 1 ST __ LF

SERIES

NO. OF CONTACTS

RIGHT ANGLE TYPE

FOR FPC/FFC, CONTACT DIRECTION

1. LOWER CONTACT TYPE
2. UPPER CONTACT TYPE

FOR AUTOMATIC MOUNTING (SMT)


PACKAGE STYLE

LEAD FREE

NOTES

- THIS PRODUCT IS THE CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND COPE WITH AUTOMATIC MOUNTING (SMT).
- SEE PART DRAWINGS FOR DIMENSIONS A~C.
- PLEASE CONSULT US IN CASE OF USING PARTS WITH * MARK.

mat'l. code				surface 58/ISO 1302		tolerance ISO 406 ISO 1101		projection		product family 58NF		CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified				mm	scale	title CAT. NO. TABLE FOR 1mm SPACING SMT CONNECTOR (Cat. No. HFW__R-1/2ST__LF)			
A				angles	linear								
				dr	DENNIS GOH	09-05-06			dwg no		sheet 2 of 9	size	
				engr	DENNIS GOH	09-05-06			10101162		A4		
				chr	DENNIS GOH	09-05-06							
				appd	JOEY NG	09-05-06							
sheet index		revision sheet										Rev. A	



PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE
1	HOUSING	PA6T RESIN GLASS REINFORCED (UL94V-0)	1	COLOR:BLACK
2	CONTACT	PHOSPHOR BRONZE	n	PLATING:TIN
3	MOUNTING PLATE		2	(LEAD FREE)


n : NO. OF CONTACTS

NOTES


1. THIS PRODUCT IS THE CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND COPS WITH AUTOMATIC MOUNTING (SMT).
2. FLATNESS OF CONTACT TERMINAL FOR HOUSING MUST BE WITHIN TOLERANCE IN Z PORTION DETAILED DRAWING.
3. THIS PRODUCT IS LOWER CONTACT TYPE CONNECTOR.
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDERING OVEN.

RECOMMENDED PC BOARD LAYOUT (COMPONENT SIDE)



BASIC PATTERN
NO.1 CONTACT
POSITION



mat'l. code				surface 58 / tolerance ISO 406			projection		product family 58NF				CODE JP						
				ISO 1302							title 1mm SPACING SURFACE MOUNT FPC/FFC CONNECTOR (Cat.No. HFW__R-1ST__LF)								
ltr ecn no dr date				tolerances unless otherwise specified															
A				angles		linear ±0.2		mm											
								scale $\propto$											
				dr		DENNIS GOH		09-05-06				dwg no				sheet 3 of 9		size	
				engr		DENNIS GOH		09-05-06				10101162				A4			
				chr		DENNIS GOH		09-05-06				type Product Customer Drawing							
				appd		JOEY NG		09-05-06											
sheet index		revision																Rev. A	
		sheet																	




DETAIL Z




PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE
1	HOUSING	PA6T RESIN GLASS REINFORCED (UL94V-0)	1	COLOR:BLACK
2	CONTACT	PHOSPHOR BRONZE	n	PLATING:TIN
3	MOUNTING PLATE		2	(LEAD FREE)

n : NO. OF CONTACTS

RECOMMENDED PC BOARD LAYOUT
(COMPONENT SIDE)BASIC PATTERN
NO.1 CONTACT
POSITION

NOTES

1. THIS PRODUCT IS THE CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND COPS WITH AUTOMATIC MOUNTING (SMT).
2. FLATNESS OF CONTACT TERMINAL FOR HOUSING MUST BE WITHIN TOLERANCE IN Z PORTION DETAILED DRAWING.
3. THIS PRODUCT IS UPPER CONTACT TYPE CONNECTOR.
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDERING OVEN.

mat'l. code				surface 58 ISO 1302			tolerance ISO 406 ISO 1101			projection 			product family 58NF						CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified			mm 			title 1mm SPACING SURFACE MOUNT FPC/FFC CONNECTOR (Cat. No. HFW__R-2ST__LF)										
A				angles	linear	±0.2														
				dr	DENNIS GOH	09-05-06				dwg no						sheet 4 of 9			size	
				engr	DENNIS GOH	09-05-06				10101162						A4				
				chr	DENNIS GOH	09-05-06														
				appd	JOEY NG	09-05-06														
sheet index		revision																Rev. A		
		sheet																		

CAT. NO. & DIMENSIONS

(NOTE4)	NO. OF CONTACTS (n)	CAT. NO. (NOTE2)	DIMENSIONS (NOTE3)		
			E MAX.	F ± 0.3	G ± 0.1
	4	HFW4R-1/2STE9LF	30.4	24	—
	5	HFW5R-1/2STE9LF	30.4	24	—
	6	HFW6R-1/2STE9LF	30.4	24	—
	7	HFW7R-1/2STE9LF	30.4	24	—
	8	HFW8R-1/2STE9LF	30.4	24	—
	9	HFW9R-1/2STE9LF	30.4	24	—
	10	HFW10R-1/2STE9LF	30.4	24	—
	11	HFW11R-1/2STE9LF	30.4	24	—
	12	HFW12R-1/2STE5LF	30.4	24	—
	13	HFW13R-1/2STE9LF	30.4	24	—
	14	HFW14R-1/2STE9LF	30.4	24	—
	15	HFW15R-1/2STE9LF	38.4	32	28.4
	16	HFW16R-1/2STE9LF	38.4	32	28.4
	17	HFW17R-1/2STE9LF	38.4	32	28.4
	18	HFW18R-1/2STE9LF	38.4	32	28.4
	19	HFW19R-1/2STE9LF	50.4	44	40.4
	20	HFW20R-1/2STE9LF	50.4	44	40.4
	21	HFW21R-1/2STE9LF	50.4	44	40.4
	22	HFW22R-1/2STE9LF	50.4	44	40.4
	23	HFW23R-1/2STE9LF	50.4	44	40.4
	24	HFW24R-1/2STE9LF	50.4	44	40.4
	25	HFW25R-1/2STE9LF	50.4	44	40.4
	26	HFW26R-1/2STE9LF	50.4	44	40.4
	27	HFW27R-1/2STE9LF	50.4	44	40.4
*	28	HFW28R-1/2STE9LF	50.4	44	40.4
*	29	HFW29R-1/2STE9LF	50.4	44	40.4

CAT. NO.

HFW (n) R - 1 ST E9 LF

SERIES

NO. OF CONTACTS

RIGHT ANGLE TYPE

FOR FPC/FFC, CONTACT DIRECTION

1. LOWER CONTACT TYPE
2. UPPER CONTACT TYPE

FOR AUTOMATIC MOUNTING (SMT)


TAPE PACKAGING FOR E9 (500pcs PER REEL)

LEAD FREE

NOTES

1. THIS PRODUCT IS THE CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND COPE WITH AUTOMATIC MOUNTING (SMT).
2. THIS CATALOG NO. INDICATES PLASTIC TAPE PACKAGED CONNECTOR.
3. SEE PART DRAWINGS FOR DIMENSIONS E~G.
4. PLEASE CONSULT US IN CASE OF USING PARTS WITH * MARK.


mat'l. code				surface 58/ISO 1302		tolerance ISO 406 ISO 1101		projection		product family 58NF		CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified				mm	scale	title CAT. NO. TABLE FOR PLASTIC TAPE PACKAGED 1mm SPACING SMT CONN. (Cat.No. HFW__R-1/2STE9LF)			
A				angles	linear								
				dr	DENNIS GOH	09-05-06			dwg no		sheet 5 of 9	size	
				enr	DENNIS GOH	09-05-06			10101162		A4		
				chr	DENNIS GOH	09-05-06			type		Product Customer Drawing		
				appd	JOEY NG	09-05-06							
sheet index		revision sheet										Rev. A	




PT. NO.	PARTS NAME	CAT. NO.	MATERIAL	Q'TY	NOTE
1	REEL	_____	POLYSTYRENE	1	COLOR:BLACK
2	PLASTIC (EMBOSSSED) TAPE	_____	PET	_____	COLOR: TRANSPARENCY (CLEAR)
3	COVER	_____	POLYESTER	_____	COLOR: TRANSPARENCY (CLEAR)
4	CONNECTOR	HFW__R-1ST__LF	SEE ATTACHED DWG.	500	LOWER CONTACT TYPE

NOTES

- THIS IS PLASTIC TAPE PACKAGED CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND COPES WITH AUTOMATIC MOUNTING (SMT).
- SEE JIS C 0806 (PACKING OF ELECTRONIC COMPONENTS ON CONTINUOUS TAPES (SURFACE MOUNTING DEVICES)) FOR SHAPE AND DIMENSIONS OF PLASTIC (EMBOSSSED) TAPE AND REEL.
- E DIMENSION IS PORTION OF THE CORE.


mat'l. code				surface 58/ISO 1302			tolerance ISO 406 ISO 1101			projection 		product family 58NF				CODE JP			
ltr	ecn no	dr	date	tolerances unless otherwise specified								title 1mm SPACING SMT CONNECTOR (Cat.No. HFW__R-1STE9LF)							
A				angles		linear ±5													
				±5°															
										scale 		dwg no sheet 6 of 9 10101162						size A4	
				dr	DENNIS GOH		09-05-06												
				enr	DENNIS GOH		09-05-06												
				chr	DENNIS GOH		09-05-06												
				appd	JOEY NG		09-05-06				type Product Customer Drawing								
sheet index		revision															Rev. A		
		sheet																	



PT. NO.	PARTS NAME	CAT. NO.	MATERIAL	Q'TY	NOTE
1	REEL	_____	POLYSTYRENE	1	COLOR: BLACK
2	PLASTIC (EMBOSSD) TAPE	_____	PET	_____	COLOR: TRANSPARENCY (CLEAR)
3	COVER	_____	POLYESTER	_____	COLOR: TRANSPARENCY (CLEAR)
4	CONNECTOR	HFW__R-2ST__LF	SEE ATTACHED DWG.	500	UPPER CONTACT TYPE


NOTES

- THIS IS PLASTIC TAPE PACKAGED CONNECTOR DESIGNED TO TERMINATE FPC/FFC AND CYPES WITH AUTOMATIC MOUNTING (SMT).
- SEE JIS C 0806 (PACKING OF ELECTRONIC COMPONENTS ON CONTINUOUS TAPES (SURFACE MOUNTING DEVICES)) FOR SHAPE AND DIMENSIONS OF PLASTIC (EMBOSSD) TAPE AND REEL.
- E DIMENSION IS PORTION OF THE CORE.

mat'l. code				surface 58 / tolerance ISO 406 ISO 1101			projection 		product family 58NF				CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified				title 1mm SPACING SMT CONNECTOR (Cat.No. HFW__R-2STE9LF)						
A				angles	linear	±5								
				±5°										
				dr	DENNIS GOH	09-05-06		dwg no 10101162				sheet 7 of 9		size A4
				engr	DENNIS GOH	09-05-06								
				chr	DENNIS GOH	09-05-06		type Product Customer Drawing						
				appd	JOEY NG	09-05-06								
sheet index	revision sheet													Rev. A

RECOMMENDED CABLE (FPC)

n : NO. OF CONDUCTORS



PT. NO.	DESCRIPTION	MATERIAL	THICKNESS (um)
1	BASE FILM	POLYIMIDE OR POLYESTER OR EQUIVALENT	25
2	CONDUCTOR	COPPER FOIL(PLATING : SOLDER 1um MIN.)	35
3	OVERLAY	POLYIMIDE OR POLYESTER OR EQUIVALENT	—
4	SUPPORTING TAPE	POLYESTER OR POLYIMIDE OR EQUIVALENT	188


NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.
3. TOTAL THICKNESS LIMIT OF EACH MATERIAL (INCLUDING ADHESIVE AGENT) IS SPECIFIED.

mat'l. code				surface 58/ISO 1302		tolerance ISO 406 ISO 1101		projection		product family 58NF		CODE JP	
ltr A				ecn no		dr		date		title		RECOMMENDED CABLE	
										(Cat. No. HFW__R-1/2__)			
				angles		linear		mm		scale		X	
				dr		DENNIS GOH		09-05-06		dwg no		sheet 8 of 9	
				enr		DENNIS GOH		09-05-06		10101162		A4	
				chr		DENNIS GOH		09-05-06		type		Product Customer Drawing	
				appd		JOEY NG		09-05-06					
sheet index		revision sheet										Rev. A	

RECOMMENDED CABLE (FFC)

n : NO. OF CONDUCTORS



(NOTE 3)	DIMENSION A	TOLERANCE B
1	0.7	0.1
2	0.6	0.07

PT. NO.	DESCRIPTION	MATERIAL	NOTE
1	INSULATOR	FLAME RESISTING POLYESTER OR EQUIVALENT	_____
2	CONDUCTOR	COPPER FOIL	PLATING: TIN OR SOLDER 1um MIN.
3	SUPPORTING TAPE	FLAME RESISTING POLYESTER OR EQUIVALENT	_____

NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.
3. BOTH COMBINATION IS ALLOWED.

mat'l. code				surface 58/ISO 1302		tolerance ISO 406 ISO 1101		projection		product family 58NF			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
A				angles	linear	RECOMMENDED CABLE (Cat. No. HFW__R-1/2__)							
								mm	scale		dwg no		
				dr	DENNIS GOH	09-05-06			sheet 9 of 9		size		
				engr	DENNIS GOH	09-05-06			10101162		A4		
				chr	DENNIS GOH	09-05-06			type		Product Customer Drawing		
				appd	JOEY NG	09-05-06							
sheet index		revision sheet										Rev. A	