

SL Series • Toroidal Power Inductors

Features

- Operating frequency to 1MHz
- High energy storage with minimum saturation
- High stability from no load to full load
- Available in both SMD and TH versions
- Manufactured in ISO 9001:2015 and ISO 14001:2015 certified Talema facility
- Meets lead free reflow level J-STD-020C
- Fully RoHS & REACH Compliant



Electrical Specifications @25°C

Test frequency: Inductance measured @10KHz / 10mV

Test voltage between windings: 500Vrms

Operating temperature range: -40°C to +130°C

Climatic Category: IEC68-1 40/125/56




Part Number	Rated Current (I _{DC})	L _N (μH) @ I rated ±20%	L _O (μH) No Load ±20%	DCR (mOhms) Nominal	Energy Storage (μJ)	Package	
						"SMD"	"THT"
SL_-3.4-1.01	3.40	1.01	1.10	9.6	6	S1	T1
SL_-1.4-6.2	1.40	6.20	7.00	62.0	6	S1	T1
SL_-1.0-17.6	1.00	17.60	23.96	117.7	9	S1	T1
SL_-4.8-3.8	4.80	3.80	5.20	17.0	44	S2	T2
SL_-2.8-9.4	2.80	9.40	12.20	41.1	37	S2	T2
SL_-1.4-29.7	1.40	29.70	35.30	144.3	29	S2	T2
SL_-0.94-114	0.94	114.00	167.00	411.2	50	S2	T2
SL_-8.0-2.5	8.00	2.50	3.80	7.8	80	S3	T3
SL_-5.4-5.1	5.40	5.10	7.50	17.5	74	S3	T3
SL_-2.7-16.2	2.70	16.20	21.90	68.5	59	S3	T3
SL_-1.3-58.1	1.30	58.10	73.00	288.8	49	S3	T3
SL_-0.9-192	0.90	192.00	292.00	534.7	78	S3	T3
SL_-0.72-383	0.72	383.00	674.00	765.0	99	S3	T3
SL_-7.8-4.9	7.80	4.90	7.90	10.9	149	S4	T4
SL_-5.5-9.0	5.50	9.00	14.00	26.1	136	S4	T4
SL_-2.7-29.1	2.70	29.10	40.50	93.8	106	S4	T4
SL_-0.74-645	0.74	645.00	1134.00	1267.2	177	S4	T4
SL_-14.3-0.81	14.30	0.81	1.25	2.3	83	SH3	--
SL_-11.5-1.32	11.50	1.32	2.10	3.2	87	SH3	--
SL_-13.9-1.68	13.90	1.68	2.80	3.3	162	SH4	--
SL_-11.4-2.5	11.40	2.50	4.20	4.9	162	SH4	--
SL_-7.2-9.3	7.20	9.30	16.00	15.1	241	S5	T5
SL_-5.1-16.1	5.10	16.10	25.90	27.3	209	S5	T5
SL_-2.6-50.0	2.60	50.00	72.90	117.2	169	S5	T5
SL_-0.71-1070	0.71	1070.00	1950.00	1616.1	270	S5	T5
SL_-12.4-3.5	12.40	3.50	6.50	5.9	269	SH5	--
SL_-10.4-4.7	10.40	4.70	8.40	7.1	254	SH5	--
SL_-15.4-5.2	15.40	5.20	10.30	5.5	617	SH6A	TH6A
SL_-10.9-9.4	10.90	9.40	17.60	11.3	558	SH6A	TH6A
Coupled Inductors							
SLC_-1.1-43.6	1.10	43.60	70.30	280.7	26	SC3	TC3
SLC_-2.7-21.9	2.70	21.90	42.90	81.0	80	SC4	--
SLC_-6.4-4.03	6.40	4.03	6.50	19.0	82	SC5	TC5
SLC_-23.8-0.53	23.80	0.53	0.88	1.2	150	SHC4	--
SLC_-21-1.1	21.00	1.10	2.10	2.1	243	SHC5	--
SLC_-22.4-2.1	22.40	2.10	4.00	3.1	527	SHC6	THC6


Note: The inductance values listed above are based on a 55°C temperature rise and 25°C ambient temperature.

Mounting Styles • SL Series Toroidal Power Inductors



Type S1 - S5




Suggested Pad Layout






Schematic




Type T1 - T5




Suggested Board Layout (Top Side View)





Type SH3 - SH6A







Suggested Pad Layout



Schematic







Type TH6A




Coupling Transformers

Type SC3 - SC5




Suggested Pad Layout



Schematic







Type SC4



Type TC3 & TC5

Suggested Pad Layout




Mounting Styles • SL Series Toroidal Power Inductors

Coupling Transformers

Surface Mount Style


Type SHC4 - SHC6



Through Hole Style

THC6

Suggested Board Layout (Top Side View)



Note:

When ordering, add "S" or "T" to the basic part number to denote preferred mounting style.

Example: SLS-3.4-1.03 for SMD or SLT-3.4-1.03 for through hole mounting.

Mounting Style	Size Code	Dimensions - Inches ± 0.010 (mm ± 0.25)				
		A	B	C	D	E
"S"	S1	0.339 (8.60)	0.339 (8.60)	0.220 (5.60)	0.268 (6.90)	0.354 (9.00)
	S2	0.433 (11.00)	0.441 (11.20)	0.303 (7.70)	0.358 (9.10)	0.413 (10.50)
	S3	0.551 (14.00)	0.559 (14.20)	0.343 (8.70)	0.461 (11.70)	0.520 (13.20)
	S4	0.591 (15.00)	0.614 (15.60)	0.390 (9.90)	0.508 (12.90)	0.551 (14.00)
	S5	0.669 (17.00)	0.701 (17.80)	0.441 (11.20)	0.591 (15.00)	0.630 (16.00)
"SH"	SH3	0.620 (15.75)	0.605 (15.37)	0.370 (9.40)	0.500 (12.70)	0.500 (12.70)
	SH4	0.670 (17.02)	0.670 (17.02)	0.390 (9.90)	0.560 (14.22)	0.490 (12.45)
	SH5	0.740 (18.80)	0.740 (18.80)	0.390 (9.90)	0.630 (16.00)	0.640 (16.26)
	SH6A	0.925 (23.50)	0.957 (24.30)	0.445 (11.30)	0.843 (21.40)	0.728 (18.50)
"SC"	SC3	0.551 (14.00)	0.630 (16.00)	0.343 (8.70)	0.530 (13.46)	0.348 (8.84)
	SC4	0.590 (14.99)	0.715 (18.16)	0.390 (9.91)	0.600 (15.24)	0.370 (9.40)
	SC5	0.662 (16.82)	0.760 (19.31)	0.413 (10.50)	0.660 (16.76)	0.445 (11.30)
"SHC"	SHC4	0.715 (18.16)	0.865 (21.97)	0.390 (9.91)	0.760 (19.30)	0.360 (9.14)
	SHC5	0.800 (20.32)	0.910 (23.11)	0.390 (9.91)	0.800 (20.32)	0.440 (11.18)
	SHC6	1.000 (25.40)	1.104 (28.05)	0.409 (10.40)	1.010 (25.65)	0.620 (15.75)

Mounting Style	Size Code	Dimensions - Inches ± 0.010 (mm ± 0.25)					
		A	B	C	D	E	Lead $\varnothing$
"T"	T1	0.339 (8.60)	0.339 (8.60)	0.201 (5.10)	0.250 (6.35)	0.250 (6.35)	0.020 (0.50)
	T2	0.433 (11.00)	0.441 (11.20)	0.280 (7.10)	0.300 (7.62)	0.300 (7.62)	0.020 (0.50)
	T3	0.551 (14.00)	0.559 (14.20)	0.311 (7.90)	0.375 (9.52)	0.375 (9.52)	0.020 (0.50)
	T4	0.591 (15.00)	0.614 (15.60)	0.358 (9.10)	0.300 (7.62)	0.500 (12.70)	0.022 (0.55)
	T5	0.669 (17.00)	0.701 (17.80)	0.409 (10.40)	0.600 (15.24)	0.500 (12.70)	.026 (0.65)
"TH"	--	--	--	--	--	--	--
	--	--	--	--	--	--	--
	--	--	--	--	--	--	--
	TH6A	0.925 (23.50)	0.957 (24.30)	0.386 (9.80)	0.650 (16.51)	0.800 (20.32)	0.031 (0.80)
"TC"	TC3	0.551 (14.00)	0.630 (16.00)	0.327 (8.30)	0.500 (12.70)	0.400 (10.16)	0.024 (0.60)
	--	--	--	--	--	--	--
	TC5	0.662 (16.82)	0.760 (19.31)	0.362 (9.20)	0.500 (12.70)	0.500 (12.70)	0.024 (0.60)
"THC"	--	--	--	--	--	--	--
	--	--	--	--	--	--	--
	THC6	1.000 (25.40)	1.104 (28.05)	0.357 (9.08)	1.000 (25.40)	0.600 (15.24)	0.028 (0.70)

Regional Locations - Design, Manufacturing, Sales & Marketing

Talema Group Regional Offices

North America

United States (Sales & Marketing)

Talema Group, LLC
PO Box 935
900 Innovation Drive
Suite 120, Rolla
Missouri 65402
Tel: +1 573-303-3675
E-Mail: sales@talemagroup.com
Web: www.talema.com

Asia

India (Design, Manufacturing, Sales & Marketing)

Administrative Office
Talema Electronic India Private Limited
Door No. 221, 1st and 2nd Floor
KJ Plaza, Opp.to Vidya Mandir School
Meyanoor Main Road
Salem - 636 004 Tamil Nadu INDIA
Tel: +91 427 - 243 3100
Fax: +91 427 - 243 3109
E-Mail: talema@talemaindia.net
Web: www.talema.com

Factory Premises
Talema Electronic India Private Limited
Plot Nos. 30, 31 Electrical and Electronic
Industrial Estate
Suramangalam
Salem - 636 005 Tamil Nadu INDIA
Tel: +91 427 - 243 3000
E-Mail: talema@talemaindia.net
Web: www.talema.com

Europe

Germany (Design, Sales & Marketing)

Talema Elektronik GmbH
Sembdnerstr. 5
82110 Germering
Tel: +49 89 - 841 00 - 0
Fax: +49 89 - 841 00 25
E-Mail: info@talema.de
Web: www.talema.com

Ireland (Design, Sales & Marketing)

Nuvotem TEO
Units W & X, Gweedore Business Park
Derrybeg, Letterkenny, Co. Donegal
Tel: +353 (0) 74 95 48666
Fax: +353 (0) 74 95 48139
E-Mail: info@nuvotem.com
Web: www.nuvotem.com

Czech Republic (Design, Manufacturing, Sales & Marketing)

NT Magnetics s.r.o.
Chebská 27
322 00 Plzeň
Tel: +420 377 - 338 351
Fax: +420 377 - 338 350
E-Mail: talema@talema.cz
Web: www.ntmagnetics.cz

Locations of Talema Group Regional Offices

