




D

D



C

C



- 1 ACCESS SLOT.
- 2 CONTACT: .000100—.000200 BRIGHT TIN—LEAD OVER .000050 NICKEL.
- 3 CONTACT: .000100—.000200 MATTE TIN OVER .000050 NICKEL.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	3	.332	.200	2	6	8-87572-5
	3	3.032	2.900	29	60	7-87572-7
	3	2.532	2.400	24	50	7-87572-2
	3	2.032	1.900	19	40	6-87572-7
	3	1.732	1.600	16	34	6-87572-4
	3	1.332	1.200	12	26	6-87572-0
OBSOLETE	3	1.032	.900	9	20	5-87572-7
	3	.932	.800	8	18	5-87572-6
	3	.832	.700	7	16	5-87572-5
	3	.732	.600	6	14	5-87572-4
	3	.632	.500	5	12	5-87572-3
	3	.532	.400	4	10	5-87572-2
OBSOLETE	3	.432	.300	3	8	5-87572-1
	2	.332	.200	2	6	3-87572-5
		3.732	3.600	36	74	3-87572-4
		3.632	3.500	35	72	3-87572-3
		3.532	3.400	34	70	3-87572-2
		3.432	3.300	33	68	3-87572-1
OBSOLETE		3.332	3.200	32	66	3-87572-0
		3.232	3.100	31	64	2-87572-9
		3.132	3.000	30	62	2-87572-8
	2	3.032	2.900	29	60	2-87572-7
		2.932	2.800	28	58	2-87572-6
		2.832	2.700	27	56	2-87572-5
OBSOLETE		2.732	2.600	26	54	2-87572-4
		2.632	2.500	25	52	2-87572-3
	2	2.532	2.400	24	50	2-87572-2
		2.432	2.300	23	48	2-87572-1
		2.332	2.200	22	46	2-87572-0
		2.232	2.100	21	44	1-87572-9
OBSOLETE		2.132	2.000	20	42	1-87572-8
	2	2.032	1.900	19	40	1-87572-7
		1.932	1.800	18	38	1-87572-6
		1.832	1.700	17	36	1-87572-5
	2	1.732	1.600	16	34	1-87572-4
		1.632	1.500	15	32	1-87572-3
OBSOLETE		1.532	1.400	14	30	1-87572-2
		1.432	1.300	13	28	1-87572-1
	2	1.332	1.200	12	26	1-87572-0
		1.232	1.100	11	24	87572-9
		1.132	1.000	10	22	87572-8
	2	1.032	.900	9	20	87572-7
OBSOLETE	2	.932	.800	8	18	87572-6
	2	.832	.700	7	16	87572-5
	2	.732	.600	6	14	87572-4
	2	.632	.500	5	12	87572-3
	2	.532	.400	4	10	87572-2
	2	.432	.300	3	8	87572-1
PLATING		C	B	A	NO OF POSN	PART NUMBER

A

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL:
HOUSING:
FLAME RETARDANT
COLOR: 1. BLACK
POSTPIPS: BRONZE

FINISH:
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S.A.SHUEY
CHK
R. FLICKER
APP'D
R. FLICKER

11OCT89
25OCT89
25OCT89

TYCO
Electronics

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME
HEADER ASSY, MOD II, DBL ROW,
.100X.100 C/L, RIGHT ANGLE,
(3) SIDED SHROUD

SIZE
A1

CAGE CODE
00779

DRAWING NO
87572

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
L1

20MAY05 10:55am US001193 H:\dmtmod\ECs\e020905c\ndia\87572-c.dwg