

MICRO SWITCH

FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

OPH-AR7

OPH-AR7

M

DRAWING
NUMBER

10

ISSUE

1

REPLACES

SR-11383

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK





REVISIONS

H	008031 J	JAS	26 APR 85
J	0073344	G J W	17 OCT 92
K	0081637	GLH	3 APR 98

FO-52851-B

DRAWN

D W V 19 JUL 62



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	
OPERATING FORCE	8-24 OZ
RELEASE FORCE	4 OZ MIN
PRETRAVEL	.219 MAX 8°
DIFFERENTIAL TRAVEL	.025 MAX
OVERTRAVEL	DO NOT OVERTRAVEL MORE THAN 25°
SWITCH-BASIC REPLACEMENT	IHS201

ELECTRICAL DATA	
CONTACT ARRANGEMENT	
S	P D T

SCALE FULL	
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
ONE PLACE	(.0) ± .030
TWO PLACE	(.00) ± .015
THREE PLACE	(.000) ± .005
ANGLES	±
THIRD ANGLE PROJECTION	
WEIGHT	

NOTES

- 1 - MOUNTING SCREW HOLE, 10-32 NF THREADS X .219 REF DEEP (8)
- 2 - 6-32 UNC X .219 REF TERMINAL SCREWS AND WASHER (SEMS) (3)
- 3 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE