


LOC	DIST	P	F	REVISIONS			DATE	APPD
				ZONE	LTR	DESCRIPTION		
G	14				C	REV PER 0G3A-0567-01	16OCT01	JR/TM

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	UL E13288 Listed
12-10 AWG STRANDED	12-10 AWG STRANDED
CS LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 PRELIMINARY - NOT FOR PRODUCTION



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -	DR 2-3-93 TA BRINKMAN CHK 2-3-93 DA PATTERSON APPD 2-3-93 DE MILLER APPD 2-3-93 JL MECKLEY PRODUCT SPEC -	2500/REEL - QTY	ON TAPE LOOSE PIECE		2-34964-1 34964	
						PACKAGE TYPE		PART NO	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE	COPPER PER ASTM B-152 ANNEALED	APPLICATION SPEC -	NAME AMP Incorporated Harrisburg, PA 17105-3608		TERMINAL, RING TONGUE BUDGET	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111							
FOR ORDER ENTRY		1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.6mm² [5,180-13,100] CIR MILS STRANDED	FINISH TIN PLATE 0.00254[0.00100] MIN THK PER MIL-T-10727	WEIGHT -	SIZE C	CAGE CODE 00779	DRAWING NO C-34964	
						SCALE 10:1		SHEET 1 OF 1	