

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [75331-0477](#)
Status: **Active**
Overview: [GbX® Backplane Connector System](#)
Description: 3-Pair GbX® Backplane Connector System, Power Module, 6 Circuits, 1.27mm Gold (Au)

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification


UL E29179

General

Product Family Backplane Connectors
Series [75331](#)
Application Backplane
Application Tooling Documents TM-622022099
Comments Blade Length A 4.50mm, B 4.50mm, C 7.50mm
Component Type Power Header
Overview [GbX® Backplane Connector System](#)
Product Name GbX®
Style N/A
UPC 822350663861

Physical

Circuits (Loaded) 6
Circuits (maximum) 6
Color - Resin Gray
Durability (mating cycles max) 200
First Mate / Last Break Yes
Flammability 94V-0
Guide to Mating Part No
Keying to Mating Part None
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Gold
Material - Plating Termination Tin-Lead
Material - Resin High Temperature Thermoplastic
Net Weight 1.555/g
Number of Columns N/A
Number of Pairs 3
Number of Rows 3
Orientation Vertical
PC Tail Length 2.28mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tube
Pitch - Mating Interface 1.85mm
Pitch - Termination Interface 1.85mm
Plating min - Mating 1.270µm
Plating min - Termination 0.762µm
Polarized to PCB Yes
Stackable Yes
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating 105°C



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[75331Series](#)

Mates With

[75292](#) GbX® Daughtercard

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Single Pin Repair Tool	0622022090
Shield Removal Tool	0622022100
3-Pair 1-Up Power Module	0622022580

Termination Interface: Style

Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact

6A

Data Rate

8.0 Gbps

Shield Type

N/A

Shielded

No

Voltage - Maximum

120V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-75331-001

GbX is a registered trademark of Amphenol Corporation.

This document was generated on 12/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75331-0477](#)