

C-MOS COMPARATOR WITH C-MOS OUTPUT

■ GENERAL DESCRIPTION


The NJU7102A and 04A dual and quad C-MOS Comparators performing wide operating voltage from 3 to 14V, low operating current and low offset voltage.

The NJU7102A and 04A operated on a single-power-supply can interface with most of TTL and C-MOS type standard logic ICs.


■ FEATURES

- Single-Power-Supply
- Wide Operating Voltage ($V_{DD}=3\sim 14V$)
- Low Operating Current ($9\mu A/\text{circuit typ.}$)
- Wide Common Mode Input Voltage ($0\sim 3.8V$ @ $V_{DD}=5V$)
- High Input Impedance
- Low Bias Current ($I_B=1pA$)
- Low Offset Voltage
- C-MOS (Push-Pull) Output
- Package Outline
 - DIP/DMP8 (NJU7102A)
 - DIP/DMP14 (NJU7104A)
- C-MOS Technology


■ PACKAGE OUTLINE




NJU7102AD



NJU7102AM




NJU7104AD




NJU7104AM

■ PIN CONFIGURATION




NJU7102AD/AM



NJU7104AD/AM

■ EQUIVALENT CIRCUIT



NJU7102A/04A

■ ABSOLUTE MAXIMUM RATINGS

(Ta=25°C)

PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	V_{DD}	16	V
Differential Input Voltage	V_{ID}	± 16 (note1)	V
Input Voltage	V_{IC}	16	V
Output Voltage	V_O	16	V
Output Current	I_O	20	mA
Power Dissipation	P_D	(DIP8) 500 (DIP14) 700 (DMP8) 300 (DMP14) 300	mW
Operating Temperature Range	T_{opr}	0~+70	°C
Storage Temperature Range	T_{stg}	-40~+125	°C

(note1) If the supply voltage (V_{DD}) is less than 16V, the input voltage must not over the V_{DD} level though 16V is limit specified.

■ ELECTRICAL CHARACTERISTICS

(Ta=25°C, $V_{DD}=5V$)

PARAMETER	SYMBOL	TEST CONDITION	NJU7102A			NJU7104A			UNIT
			MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	
Operating Voltage	V_{DD}		3	-	14	3	-	14	V
Input Offset Voltage	V_{IO}	$V_{IC}=V_{ICMin}$ (note2)	-	1.2	12	-	1.2	12	mV
Input Offset Current	I_{IO}		-	1	-	-	1	-	pA
Input Bias Current	I_{IB}		-	1	-	-	1	-	pA
Input Common Mode Voltage Range	V_{ICM}		0	-	3.8	0	-	3.8	V
Output Voltage	V_{OH}	$V_{ID}=+1V, I_{OH}=+5V$	4.5	4.7	-	4.5	4.7	-	V
	V_{OL}	$V_{ID}=+1V, I_{OL}=+6mA$	-	0.22	0.30	-	0.234	0.30	V
Common Mode Rejection Ratio	CMR	$V_{IC}=V_{ICMin}$	-	82	-	-	78	-	dB
Supply Voltage Rejection Ratio	SVR	$V_{DD}=5\sim 10V$	-	90	-	-	92	-	dB
Operating Current	I_{DD}	No Load, $V_O=0V$	-	18	40	-	36	80	μA


(note2) This condition is available for operating voltage $V_{DD}=5\sim 10V$ and driving voltage is over 4.5V or under 0.3V.

■ SWITCHING CHARACTERISTICS


(Ta=25°C, $V_{DD}=5V, f=10kHz, C_L=15pF$)

PARAMETER	SYMBOL	CONDITIONS		NJU7102A			NJU7104A			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
Propagation Delay High to Low	t_{PHL}	$V_{IC}=0V$	Over Drive=5mV	-	3.0	-	-	2.3	-	μs
			TTL level step	-	0.17	-	-	0.17	-	
Propagation Delay Low to High	t_{PLH}	$V_{IC}=0V$	Over Drive=5mV	-	1.9	-	-	1.3	-	μs
			TTL level step	-	0.8	-	-	0.8	-	
Output Signal Falling Time	t_{THL}	Over Drive=50mV		-	30	-	-	30	-	ns
Output Signal Rising Time	t_{TLH}	Over Drive=50mV		-	70	-	-	70	-	ns

■ MEASUREMENT CIRCUIT



■ TIMING WAVEFORM



[CAUTION]

The specifications on this databook are only given for information, without any guarantee as regards either mistakes or omissions. The application circuits in this databook are described only to show representative usages of the product and not intended for the guarantee or permission of any right including the industrial rights.