


NO	DESCRIPTION	DATE
①	MODIFICATION CENTER CONTACT⑦ BACKGROUND FORMAT UPDATED	01.13.10'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-900 MHz
1.2 NOMINAL IMPEDANCE: 50 OHM

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
2.2 CENTER CONTACT: BRASS PER JIS-C3604
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -55° C TO +125° C

7	CENTER CONTACT	BRASS	1	GOLD
6	INSULATION	TEFLON	1	NONE
5	WASHER	BRASS	1	NONE
4	BODY	BRASS	1	NICKEL 100 μ" MIN.
3	GASKET	SILICONE	1	RED
2	INSULATION	TEFLON	1	NONE
1	SHELL	BRASS	1	NICKEL 100 μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED by _____ DATE: _____

DESCRIPTION			FME PLUG - TNC PLUG									
製圖	DRAWN	TOLERANCE		品名	23-12 T.G.N			日期	DATE	版次	REV.	
	Yoko	.X	±0.2	TITLE	\ROHS COMPLIANT (50Ω)				04.27.93'			
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.		23-0044				
	Jacky	.XXX	±0.05		mm(in)							
認定	APPROVAL	.XXX	±0.05	比例	SCALE	佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.						
	Lewis	ANGLE	±5°		4:1							