



Microsemi Corp.

The diode experts

SCOTTSDALE, AZ

For more information call:
(602) 941-6300

**1N5221
thru
1N5281
DO-35**

FEATURES

- 2.4 THRU 200 VOLTS
- COMPACT PACKAGE
- CONSULT FACTORY FOR VOLTAGES ABOVE 200 V

MAXIMUM RATINGS

Operating and Storage Temperature: -65°C to $+200^{\circ}\text{C}$
 DC Power Dissipation: 500 mW
 Power Derating: 4.0 mW/ $^{\circ}\text{C}$ above 50°C
 Forward Voltage @ 200 mA: 1.1 Volts

ELECTRICAL CHARACTERISTICS

See following page for table of parameter values. (Fig. 3)

Table as shown on following page (Fig. 3) lists JEDEC type numbers, which indicate a tolerance of $\pm 20\%$ with guaranteed limits on only V_Z , I_r , and V_f . Devices with guaranteed limits on all six parameters are indicated by suffix 'A' for $\pm 10\%$ tolerance and suffix 'B' for $\pm 5\%$ tolerance. Also available with suffix C or D which indicates 2% and 1% tolerance respectively.




FIGURE 2

POWER DERATING CURVE

**SILICON
500 mW
ZENER DIODES**




FIGURE 1

All dimensions in $\frac{\text{INCH}}{\text{m.m.}}$

MECHANICAL CHARACTERISTICS

CASE: Hermetically sealed glass case. DO-35.

FINISH: All external surfaces are corrosion resistant and leads solderable.

THERMAL RESISTANCE: $250^{\circ}\text{C}/\text{W}$ (Maximum) junction to lead at 0.375-inches from body.

POLARITY: Diode to be operated with the banded end positive with respect to the opposite end.

1N5221 thru 1N5281 DO-35

*ELECTRICAL CHARACTERISTICS @ 25°C

JEDEC Type No. Note 1	Nominal Zener Voltage V _Z @ I _{ZT} Volts	Test Current I _{ZT} mA	Max Zener Impedance A & B Suffix Only Note 2		Max Reverse Leakage Current				Max Zener Voltage Temp. Coeff. (A & B Suffix Only) α _{VZ} (%/°C) Note 3
			Z _{1T} @ I _{ZT} Ohms	Z _{2K} @ I _{ZK} = 0.25 mA Ohms	A, B, C & D Suffix Only			Non-Suffix I _L @ V _L Used For Suffix A μA	
					I _L μA	@ V _L Volts	A, B, C & D		
1N5221	2.4	20	30	1200	100	0.95	1.0	200	-0.085
1N5222	2.5	20	30	1250	100	0.95	1.0	200	-0.085
1N5223	2.7	20	30	1300	75	0.95	1.0	150	-0.080
1N5224	2.8	20	30	1400	75	0.95	1.0	150	-0.080
1N5225	3.0	20	29	1600	50	0.95	1.0	100	-0.075
1N5226	3.3	20	28	1600	25	0.95	1.0	100	-0.070
1N5227	3.6	20	24	1700	15	0.95	1.0	100	-0.065
1N5228	3.9	20	23	1900	10	0.95	1.0	75	-0.060
1N5229	4.3	20	22	2000	5.0	0.95	1.0	50	±0.055
1N5230	4.7	20	19	1900	5.0	1.9	2.0	50	±0.030
1N5231	5.1	20	17	1600	5.0	1.9	2.0	50	±0.030
1N5232	5.6	20	11	1600	5.0	2.9	3.0	50	±0.038
1N5233	6.0	20	7.0	1600	5.0	3.3	3.5	50	±0.038
1N5234	6.2	20	7.0	1000	5.0	3.8	4.0	50	±0.045
1N5235	6.8	20	5.0	750	3.0	4.8	5.0	30	±0.050
1N5236	7.5	20	6.0	500	3.0	5.7	6.0	30	±0.058
1N5237	8.2	20	8.0	500	3.0	6.2	6.5	30	±0.062
1N5238	8.7	20	8.0	600	3.0	6.2	6.5	30	±0.065
1N5239	9.1	20	10	600	3.0	6.7	7.0	30	±0.068
1N5240	10	20	17	600	3.0	7.6	8.0	30	±0.075
1N5241	11	20	22	600	2.0	8.0	8.4	30	±0.076
1N5242	12	20	30	600	1.0	8.7	9.1	10	±0.077
1N5243	13	9.5	13	600	0.5	9.4	9.9	10	±0.079
1N5244	14	9.0	15	600	0.1	9.5	10	10	±0.082
1N5245	15	8.5	16	600	0.1	10.5	11	10	±0.082
1N5246	16	7.8	17	600	0.1	11.4	12	10	±0.083
1N5247	17	7.4	19	600	0.1	12.4	13	10	±0.084
1N5248	18	7.0	21	600	0.1	13.3	14	10	±0.085
1N5249	19	6.6	23	600	0.1	13.3	14	10	±0.086
1N5250	20	6.2	25	600	0.1	14.3	15	10	±0.086
1N5251	22	5.6	29	600	0.1	16.2	17	10	±0.087
1N5252	24	5.2	33	600	0.1	17.1	18	10	±0.088
1N5253	25	5.0	35	600	0.1	18.1	19	10	±0.089
1N5254	27	4.6	41	600	0.1	20	21	10	±0.090
1N5255	28	4.5	44	600	0.1	20	21	10	±0.091
1N5256	30	4.2	49	600	0.1	22	23	10	±0.091
1N5257	33	3.8	58	700	0.1	24	25	10	±0.092
1N5258	36	3.4	70	700	0.1	26	27	10	±0.093
1N5259	39	3.2	80	800	0.1	29	30	10	±0.094
1N5260	43	3.0	93	900	0.1	31	33	10	±0.095
1N5261	47	2.7	105	1000	0.1	34	36	10	±0.095
1N5262	51	2.5	125	1100	0.1	37	39	10	±0.096
1N5263	56	2.2	150	1300	0.1	41	43	10	±0.096
1N5264	60	2.1	170	1400	0.1	44	46	10	±0.097
1N5265	62	2.0	185	1400	0.1	45	47	10	±0.097
1N5266	68	1.8	230	1600	0.1	49	52	10	±0.097
1N5267	75	1.7	270	1700	0.1	53	56	10	±0.098
1N5268	82	1.5	330	2000	0.1	59	62	10	±0.098
1N5269	87	1.4	370	2200	0.1	65	68	10	±0.099
1N5270	91	1.4	400	2300	0.1	66	69	10	±0.099
1N5271	100	1.3	500	2600	0.1	72	76	10	±0.110
1N5272	110	1.1	750	3000	0.1	80	84	10	±0.110
1N5273	120	1.0	900	4000	0.1	86	91	10	±0.110
1N5274	130	0.95	1100	4500	0.1	94	99	10	±0.110
1N5275	140	0.90	1300	4500	0.1	101	106	10	±0.110
1N5276	150	0.85	1500	5000	0.1	108	114	10	±0.110
1N5277	160	0.80	1700	5500	0.1	116	122	10	±0.110
1N5278	170	0.74	1900	5500	0.1	123	129	10	±0.110
1N5279	180	0.68	2200	6000	0.1	130	137	10	±0.110
1N5280	190	0.66	2400	6500	0.1	137	144	10	±0.110
1N5281	200	0.65	2500	7000	0.1	144	152	10	±0.110

*JEDEC registered data

FIGURE 3

NOTE 1 The electrical characteristics are measured after allowing the device to stabilize for 20 seconds when mounted with a 3/64" minimum lead length from the case.

NOTE 2 The zener impedance is derived from the 60 HZ ac voltage, which results when an ac current having an r.m.s. value equal to 10% of the DC zener current (I_{ZT} or I_{ZK}) is superimposed on I_{ZT} or I_{ZK} . Zener impedance is measured at two points to insure a sharp knee on the breakdown curve, thereby, eliminating unstable units.

NOTE 3 Temperature coefficient (α_{VZ}).

Test conditions for temperature coefficient are as follows:

- $I_{ZT} = 7.5$ mA, $T_1 = 25^\circ\text{C}$,
 $T_2 = 125^\circ\text{C}$ (1N5221A, B thru 1N5242A, B.)
- $I_{ZT} = \text{Rated } I_{ZT}$, $T_1 = 25^\circ\text{C}$,
 $T_2 = 125^\circ\text{C}$ (1N5243A, B thru 1N5281A, B.)

Device to be temperature stabilized with current applied prior to reading breakdown voltage at the specified ambient temperature.

1N5221 thru 1N5281 DO-35




FIGURE 4
CAPACITANCE VS. ZENER VOLTAGE
(TYPICAL)