



2.3 Modelli NTC*WH*

Condizioni di immagazzinamento	-50T105 °C
Campo di lavoro	-50T105 °C
Conessioni	Terminali spellati, dimensioni: 5±1 mm
Sensore	NTC 10 kΩ ±1% a 25 °C Beta 3435
Fattore di dissipazione (in aria)	ca. / approx. 2,2 mW/°C
Cost. term. nel tempo (in aria)	ca. / approx. 30 s
Cavo	Bipolare doppia guaina di isolamento, AWG22 in rame stagnato con resistenza elettrica ≤63 Ω/km - Isolante: tipo TPE specifico ad immersione in acqua su guaina esterna, PPcop. su conduttori interni, Ø esterno 3,5 mm max
Grado di protezione elemento sensibile	IP68
Contenitore elemento sensibile	PPcop. con cappuccio AISI 316 esterno
Classificazione secondo la protezione contro le scosse elettriche (elemento sensibile e cavo)	Isolamento supplementare per 250 Vac;
Categoria di resistenza al calore e al fuoco	Non propagante la fiamma
Certificazioni	NSF



Versione 1


* = vedi tabella codici presente nel listino prezzi




Versione 2

Accessori

Pozzetto: ottone nichelato - 1413306AXX




Pozzetto 2: AISI 316 - cod. 1413309AXX



Nota:

- bloccaggio cavo con passacavo PG7 - IP68 applicato sull' estremità esagonale
- è disponibile il kit completo di pozzetto e pressacavo

Raccordo a compressione con ogiva metallica - cod. 1309589AXX



Item # NTC015WP00, -NO LONGER AVAILABLE
Price



-NO LONGER AVAILABLE

The NTC015WP00 sensors are now phased out; the product has been replaced by theNTC015WH01. The new NTC*WH00 family sensors have the same technical specifications and offer a higher IP (IP68 for permanent immersion); these have better performance in extreme environmental conditions, specifically they can withstand immersion, condensate and ice formation indefinitely.

· [AVAILABILITY](#) · [SPECIFICATIONS](#) · [PACKAGE & HANDLING FEE](#) · [NORTH AMERICA PRICING](#)

AVAILABILITY

Inventory Status	NO LONGER AVAILABLE
Inventory updated on:	NO LONGER AVAILABLE

SPECIFICATIONS

Shipping Weight	2.1 Pound
Description	NTC (10K Ohm) Temperature Sensors NTC bulb temp Sensor, 5 ft cable, -58 to 221 °F, IP68
Temperature Range	-58 to 221 °F
Cable Length	5 ft

PACKAGE & HANDLING FEE

Any order under \$100.00 net will incur a \$25.00 package an handling fee. This fee will be applied to the order at time of shipping.

NORTH AMERICA PRICING

Note on Price	Applicable to North America only.
---------------	-----------------------------------