

Description

The TH7107 FSK/ASK/FM transmitter IC is designed for applications in the European 433MHz industrial-science-medical (ISM) band, according to the EN 300 220 telecommunications standard. It can also be used for any other system with carrier frequencies ranging from 315 to 470 MHz (e.g. for applications in the US 315MHz ISM band).

The transmitter's carrier frequency f_c is determined by the frequency of the reference crystal f_{ref} that is used. The integrated PLL synthesizer ensures that each RF value, ranging from 315 to 470 MHz, can be achieved by using a crystal with reference frequency according to: $f_{ref} = f_c/N$, where $N = 32$ is the PLL feedback divider ratio

Features


- q fully integrated, PLL-stabilized VCO
- q FSK through crystal pulling allows modulation from DC to 20 kbit/s
- q high deviation possible for wideband data transmission
- q ASK achieved by on/off keying of internal power amplifier
- q FM possible with external varactor
- q wide power supply range from 2.1 to 5.5 V
- q flexible frequency range from 315 to 470 MHz
- q high over-all frequency accuracy
- q adjustable output power range from -12 to +3 dBm
- q adjustable current consumption from 4.8 to 11.5 mA
- q deviation and center frequency independently adjustable
- q very low standby current
- q differential output well-suited for loop antenna
- q external clock available for μ C drive, down to 1.9 V supply
- q "clock only" mode
- q conforms to EN 300 220 standard

Applications

- q keyless car security and central locking
- q low power telemetry
- q alarm systems
- q general digital data transmission
- q general analog audio signal transmission

Block Diagram with External Components

Fig. 1: TH7107 block diagram



Theory of Operation

FSK Modulation

A Colpitts crystal oscillator (XOSC) is used as the reference oscillator of a phase-locked loop (PLL) synthesizer. FSK modulation is achieved by pulling the crystal (XTAL) through the data. So a CMOS-compatible data stream applied at input DATA digitally modulates the XOSC. Two external pulling capacitors C_{x1} and C_{x2} allow the FSK deviation and center frequency to be adjusted independently. At DATA = LOW C_{x2} is connected in parallel to C_{x1} leading to the low-frequency component of the FSK spectrum (f_{\min}); while at DATA = HIGH C_{x2} is deactivated and the XOSC is set to its high frequency, leading to f_{\max} .

An external reference signal can be directly AC-coupled to pin RO1. Then the TH7107 is used without an XTAL. The reference signal has to contain the FSK (or FM) and sets the carrier frequency.

ASK Modulation

The TH7107 can be ASK-modulated by applying data directly at pin PS. This turns the PA on and off and therefore leads to an ASK signal at the output.

Frequency Modulation (FM)

For FM operation an external varactor is required. It simply acts as a pulling capacitor connected in series to the crystal. Then the analog modulation signal, applied through a series resistor, directly modulates the XOSC.

General

Other parts of the TH7107 transmitter are the fully integrated voltage-controlled oscillator (VCO), the divide-by-32 divider (div32), the phase-frequency detector (PFD) and the charge pump. An external loop filter between pins LF1 and LF2 de-

termines the dynamic behaviour of the PLL and suppresses reference spurious signals. The VCO's output signal feeds the power amplifier (PA). RF signal power P_o can be adjusted in six steps from $P_o = -12$ to $+3$ dBm either by changing the value of resistor R_{ps} or by varying the voltage V_{ps} at pin PS. The open-collector differential output (OUT1, OUT2) can be used to either directly drive a loop antenna or to be converted to a single-ended impedance by means of a balanced-to-unbalanced (balun) transformer. For maximum available output power, the differential output should be matched to a load of approx. 2 to 3 k Ω .

Bandgap biasing ensures stable operation of the IC at a power supply range of 2.1 to 5.5 V. The mode control logic allows four different modes of operation as listed in the following table. The mode control pins ENCK and ENTX are internally terminated to pull-down and pull-up resistors, respectively. This guarantees that the whole circuit is shut down if these pins are left floating.

| ENCK | ENTX | Mode | Description |
|------|------|------------|---|
| 0 | 0 | all OFF | whole circuit in standby |
| 0 | 1 | TX only | TX functionality only, no clock available |
| 1 | 0 | clock only | TX in standby and clock available |
| 1 | 1 | all ON | TX functional and clock available |

The clock output CKOUT can be used to drive a μ C. This output can be activated by the ENCK pin as required for any specific application. Clock frequency is 1/4 of the reference crystal frequency.

Electrical Characteristics

Absolute Maximum Ratings

| Parameter | Symbol | Condition | Min | Max | Unit |
|---------------------|-----------|--------------------|------|--------------|------|
| supply voltage | V_{cc} | | -0.3 | 7.0 | V |
| input voltage | V_{in} | @ DATA, ENCK, ENTX | -0.3 | $V_{CC}+0.3$ | V |
| input current | I_{in} | @ DATA, ENCK, ENTX | -1.0 | 1.0 | mA |
| storage temperature | T_{str} | | -40 | 150 | °C |

Operating Conditions

| Parameter | Symbol | Min | Max | Unit |
|---------------------|-----------|-----|-----|------|
| supply voltage | V_{cc} | 2.1 | 5.5 | V |
| ambient temperature | T_a | -40 | 85 | °C |
| VCO frequency | f_c | 312 | 475 | MHz |
| XOSC frequency | f_{ref} | 9.5 | 15 | MHz |
| clock frequency | f_{clk} | 2.4 | 3.8 | MHz |

DC Characteristics

T_a = -40 to +85 °C,
 V_{cc} = 2.1 to 5.5 V,
typical values at T_a = 23 °C
and V_{cc} = 3 V

| Parameter | Symbol | Condition | Min | Typ | Max | Unit |
|---|------------|---------------------------------------|--------------|-------|--------------|------|
| standby current | I_{stb} | ENCK=0, ENTX=0 | | < 0.1 | 0.1 | µA |
| clock only current | I_{clk} | ENCK=1, ENTX=0 | 0.7 | 0.9 | 1.1 | mA |
| operating current | I_{cc} | ENCK=1, ENTX=1, $R_{ps}=47k\Omega$ | 7 | 9 | 10 | mA |
| input HIGH voltage | V_{HIGH} | @ DATA, ENCK, ENTX | $0.7*V_{cc}$ | | $V_{cc}+0.3$ | V |
| input LOW voltage | V_{LOW} | @ DATA, ENCK, ENTX | -0.3 | | $0.3*V_{cc}$ | V |
| input current @ $V_{LOW} < V_{in} < V_{HIGH}$ | I_{in} | @ DATA, ENCK, ENTX | -10 | | 10 | µA |

AC Characteristics

$T_a = -40$ to $+85$ °C,
 $V_{cc} = 2.1$ to 5.5 V,
typical values at $T_a = 23$ °C
and $V_{cc} = 3$ V

(ENCK = 1 ENTX = 1, $R_{ps} = 56$ kΩ, $f_c = 433.6$ MHz, test circuit shown in **Fig. 2**)

| Parameter | Symbol | Condition | Min | Typ | Max | Unit |
|---------------------------------|------------------|--|-----|------|-----|----------|
| output power | P_o | DATA = HIGH | | 0 | | dBm |
| max. data rate at FSK | R_{FSK} | | | 20 | | kbit/s |
| FSK deviation | Δf_{FSK} | adjustable with $C_{x1}, C_{x2},$, ref. to Fig. 2 | | ±50 | | kHz |
| max. data rate at ASK | R_{ASK} | DATA = LOW | | 40 | | kbit/s |
| max. modulation frequency at FM | f_{mod} | DATA = HIGH | | 15 | | kHz |
| FM deviation | Δf_{FM} | adjustable with varactor and V_{FM} | | ±6 | | kHz |
| reference spurs | P_{ref} | @ $f_c \pm f_{ref}$ | | -44 | | dBm |
| clock spurs | P_{clk} | @ $f_c \pm f_{clk}$ | | -44 | | dBm |
| harmonic content | P_{harm} | | | -40 | | dBm |
| phase noise | L | DATA = HIGH @ $f_c \pm 500$ kHz | | -87 | | dBc/Hz |
| VCO gain | k_{vco} | | | 200 | | MHz/V |
| charge pump current | I_{CP} | | | ±260 | | µA |
| clock volt. swing | V_{CKOUT} | $C_{load} = 5$ pF | | 2 | | V_{pp} |
| start-up time | t_{on} | from "all OFF" to any other mode | | 0.8 | | ms |


Output Power Selection

typical values at $T_a = 23$ °C
and $V_{cc} = 3$ V,

(ENCK = 1, ENTX = 1, $f_c = 433.6$ MHz, test circuit shown in **Fig. 2**, C2 and C3 to adjust for P_o and P_{harm})


| R_{ps} / kW | 3 68 | 56 | 47 | 39 | 27 | 15 |
|------------------|------|------|------|------|------|-------|
| V_{ps} / V | 3 2 | 1.2 | 0.9 | 0.7 | 0.5 | 0.3 |
| I_{cc} / mA | 11.5 | 8.6 | 7.3 | 6.2 | 5.3 | 4.8 |
| P_o / dBm | 3.0 | 0.5 | -1.0 | -4.0 | -8.0 | -12.0 |
| P_{harm} / dBm | ≤-36 | ≤-40 | ≤-40 | ≤-45 | ≤-45 | ≤-50 |
| C2 / pF | TBD | 1.8 | TBD | TBD | TBD | TBD |
| C3 / pF | TBD | 3.9 | TBD | TBD | TBD | TBD |

Pin Description



| Pin # | Pin Name | Description |
|-------|----------|--|
| 1 | LF1 | charge pump output, input to loopfilter |
| 2 | SUB | negative power supply, substrate connection |
| 3 | DATA | FSK data input, CMOS-compatible |
| 4 | RO2 | XOSC FSK pulling pin, switch to GND or OPEN |
| 5 | RO1 | XOSC connection to XTAL, base of bipolar transistor |
| 6 | ENTX | mode control input, CMOS-compatible with internal pull-up res. |
| 7 | ENCK | mode control input, CMOS-compatible with internal pull-down res. |
| 8 | CKOUT | clock output |
| 9 | PS | power-select and ASK input, high-impedance comparator logic |
| 10 | VCC | positive power supply |
| 11 | VEE | negative power supply |
| 12 | OUT2 | differential power amp output, open collector |
| 13 | OUT1 | differential power amp output, open collector |
| 14 | VEE | negative power supply |
| 15 | VCC | positive power supply |
| 16 | LF2 | VCO tuning input, output from loopfilter |

Package Information




SSOP 16 150 mil

Dimension : mm

| | D | E1 | E | A | A1 | e | b | L | Copl | α |
|-----|------|------|------|------|------|-------|------|------|------|----|
| min | 4.80 | 3.81 | 5.79 | 1.35 | 0.10 | 0.635 | 0.20 | 0.41 | | 0° |
| max | 5.00 | 3.99 | 6.20 | 1.75 | 0.25 | | 0.30 | 1.27 | 0.10 | 8° |

Test Circuit

Fig. 2: test circuit for FSK, ASK and FM; with 50Ω matching network



test circuit component list

| Part | Size | Value | Tolerance | Description |
|------|--------|----------------------------|------------------------------------|--|
| CF1 | 0603 | 10 nF | ±10% | loopfilter capacitor |
| CF2 | 0603 | 12 pF | ±10% | loopfilter capacitor |
| CX1 | 0603 | 12 pF | ±5% | XOSC capacitor, for FSK only |
| CX2 | 0603 | 100 pF | ±5% | XOSC capacitor, for FSK only |
| CX3 | 0603 | 1 nF | ±10% | XOSC capacitor, for FM only |
| C1 | 0603 | 2.7 pF | ±5% | impedance matching capacitor |
| C2 | 0805 | 1.8 pF | ±5% | impedance matching capacitor |
| C3 | 0805 | 3.9 pF | ±5% | impedance matching capacitor |
| C4 | 0603 | 150 pF | ±5% | impedance matching capacitor |
| C5 | 0603 | 330 pF | ±10% | blocking capacitor |
| C6 | 0603 | 330 pF | ±10% | blocking capacitor |
| C7 | 1206 | 220 nF | ±20% | blocking capacitor |
| L1 | 0603 | 22 nH | ±5% | impedance matching inductor |
| L2 | 0603 | 22 nH | ±5% | impedance matching inductor |
| L3 | 0805 | 33 nH | ±5% | impedance matching inductor |
| RF1 | 0805 | 2 kΩ | ±10% | loopfilter resistor |
| RF2 | 0805 | 4.3 kΩ | ±10% | loopfilter resistor |
| RPS | 0805 | 56 kΩ | ±10% | power-select resistor |
| R1 | 0805 | 470 kΩ | ±10% | optional pull-up resistor |
| R2 | 0805 | 30 kΩ | ±10% | varactor bias resistor, for FM only |
| R3 | 0805 | 0 Ω | ±10% | ASK jumper, for ASK only |
| V1 | SOD323 | BB535 | | varactor diode, for FM only |
| XTAL | HC49/S | 13.55 MHz fundamental wave | ±30ppm calibration ±30ppm temp. | crystal, $C_{load} = 10\text{pF}$, $C_{0,max} = 4\text{pF}$, $C_m = 20\text{fF}$, $R_m = 10 - 20\Omega$ |

Spectrum Plots

All plots depict TH7107's typical performance at $V_{cc} = 3.0$ V and $T_a = 23$ °C, derived with the test circuit shown **Fig. 2**.

Fig. 3: RF output signal and spurious emissions, CW mode (DATA = HIGH)




Fig. 4: Single-sideband phase noise at 500 kHz offset, CW mode (DATA = HIGH)






Fig. 5: FSK modulation with $R_{FSK} = 6.6$ kbit/sFig. 6: ASK modulation with $R_{ASK} = 4$ kbit/s, DATA = HIGHFig. 7: FM with $f_{mod} = 2$ kHz, FM input signal with $1 V_{pp}$ around $1.5 V_{DC}$, DATA = HIGH