




THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION SEP ,2005.							LOC J		DIST 		REVISIONS 変更									
© COPYRIGHT 2005 By --				ALL RIGHTS RESERVED.									P		LTR		DESCRIPTION		DATE		DWN		APVD	
				NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.									F4		REVISED(ADD A NEW PN)		23JUNE2014		B.L		J.L			
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	—	0.5	10.55	—	—	1.1	1.1	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 2)	WITHOUT FLANGE TYPE (SEE SHEET 6)	9—1747981—2										
AVAILABLE	WITH P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITH BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	9—1747981—1										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	14.3	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	8—1747981—2										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	CLEAR TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	8—1747981—1										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITH BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	3—1747981—1										
NOT AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	16.3	#4—40 UNC	0.5	10.55	12.75	10.08	2.2	1.8	WITH BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	2—1747981—4										
AVAILABLE	WITHOUT P/N	Au 0.76um MIN	16.3	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	2—1747981—3										
NOT AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	#4—40 UNC	0.5	10.05	12.75	10.08	2.2	1.8	WITHOUT BOSS	HARDTRAY PACKING (—)	WITH FLANGE TYPE (SEE SHEET 7)	2—1747981—2										
AVAILABLE	WITHOUT P/N	Au 0.76um MIN	—	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	2—1747981—1										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	1.0	10.55	12.75	10.08	1.5	1.5	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—8										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	16.3	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—7										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 5)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—6										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	14.3	M3 x 0.5	0.5	10.05	10.95	7.98	1.5	1.5	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—5										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—4										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	#4—40 UNC	0.5	10.05	12.75	10.08	2.2	1.8	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—3										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	0.5	10.05	10.95	7.98	1.5	1.5	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—2										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—1										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	—	0.5	10.05	—	—	1.5	1.5	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 2)	WITHOUT FLANGE TYPE (SEE SHEET 6)	1747981—2										
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	—	0.5	10.05	—	—	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 2)	WITHOUT FLANGE TYPE (SEE SHEET 6)	1747981—1										
TOOL STATUS	PART NUMBER MARKING	CONTACT AREA PLATING SPEC J	DIM H	SCREW SIZE DIM G	DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	BOSS	PACKING	CONNECTOR TYPE	PART NUMBER										
1 CONTACT COPLANALITY IS 0.1 MAXIMUM. THIS DIMENSION MEANS CENTER OF THE POCKET. FINISH CONTACT: CONTACT AREA J: SEE TABLE 2um MIN Sn PLATING ON SOLDERING AREA 2um MIN Ni UNDER PLATING ALL OVER SHELL: 1um MIN Sn PLATING ALL OVER 1um MIN Ni UNDER PLATING ALL OVER REFER TO THE TABLE FOR BOSS. SCREW SIZE PART NUMBER MAKING											THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN Y.HIRATA 15SEP2005		TE Connectivity HDMI 19 POS RECEPTACLE ASSY SMT TYPE —LEAD FREE—							
DIMENSIONS: 単位： 耗 mm					TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差			CHK T.KIMURA 15SEP2005		NAME 名称														
					0 PLC ± 0.2 1 PLC ± 0.2 2 PLC ± 0.2 3 PLC ± 0.2 4 PLC ± 0.2 ANGLES ± —			APVD K.IKEGAMI 15SEP2005		PRODUCT SPEC 製品規格 108—78180—1														
								APPLICATION SPEC 取付適用規格		SIZE CAGE CODE DRAWING NO 番号 A300779C—1747981														
MATERIAL 材料					FINISH 仕上			WEIGHT		CUSTOMER DRAWING		SCALE 尺度 NTS		SHEET 1 OF 8		REV F4								


LOC	DIST	REVISIONS				DATE	DWN	APVD
		P	LTR	DESCRIPTION	變更			
J			-	SEE SHEET 1		-	-	-

NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: 单位: 耗 mm		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD	NAME 名称			
0 PLC ± 0.2		PRODUCT SPEC 製品規格	HDMI 19 POS			
1 PLC ± 0.2		108-78180-1	RECEPTACLE ASSY SMT TYPE			
2 PLC ± 0.2		APPLICATION SPEC 取付適用規格	-LEAD FREE-			
3 PLC ± 0.2		WEIGHT	SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
4 PLC ± 0.2			A3	00779	C-1747981	
ANGLES ± -		CUSTOMER DRAWING	SCALE 尺度	NTS	SHEET 2 of 8	REV F4
FINISH 仕上						
MATERIAL 材料						








NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.

THIS DRAWING IS A CONTROLLED DOCUMENT.


DIMENSIONS: 単位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
	0 PLC ± 0.2 1 PLC ± 0.2 2 PLC ± 0.2 3 PLC ± 0.2 4 PLC ± 0.2 ANGLES ± 0.3 FINISH 仕上 ± 0.1
MATERIAL 材料	

40	WITH FLANGE TYPE	1-1747981-6
QTY	CONNECTOR TYPE	PART NUMBER
DWN	TE Connectivity	
CHK		
APVD		
PRODUCT SPEC 製品規格		
APPLICATION SPEC 取付適用規格	HDMI 19 POS RECEPTACLE ASSY SMT TYPE -LEAD FREE-	
WEIGHT	SIZE A3	CAGE CODE 00779
CUSTOMER DRAWING	DRAWING NO 番号 C-1747981	RESTRICTED TO -
SCALE 尺度 NTS		SHEET 5 OF 8
		REV F4

LOC	DIST	REVISIONS				DATE	DWN	APVD
		P	LTR	DESCRIPTION	變更			
J		-	-	SEE SHEET 1		-	-	-



P.C.B LAYOUT
SHOWN AS CONNECTOR MOUNTING SIDE
TOLERANCE: NON-CUMULATIVE
(REFERENCE)



PANEL CUT OUT DIMENSION
(REFERENCE)

CONNECTOR WITHOUT FLANGE TYPE

NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL
OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.

	POLYIMIDE	1	POLYIMIDE TAPE	④
③	COPPER ALLOY	19	CONTACT	③
③	COPPER ALLOY	1	SHELL	②
	THERMOPLASTIC UL94V-0, BLACK COLOR	1	HOUSING	①
FINISH	MATERIAL	QTY	DISCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: 單位: 耗 mm		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD	NAME 名称			
0 PLC ± 0.2		PRODUCT SPEC 製品規格	HDMI 19 POS			
1 PLC ± 0.2		108-78180-1	RECEPTACLE ASSY SMT TYPE			
2 PLC ± 0.2		APPLICATION SPEC 取付適用規格	-LEAD FREE-			
3 PLC ± 0.2		WEIGHT	SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
4 PLC ± 0.2		CUSTOMER DRAWING	A3	00779	C-1747981	-
ANGLES ± 0.1			SCALE 尺度	4:1	SHEET 6 of 8	REV F4
FINISH 仕上						
MATERIAL 材料						

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION SEP , 2005.

© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

LOC
J

DIST
/

REVISIONS

變更

P

LTR

DESCRIPTION

DATE

DWN

APVD

-


SEE SHEET 1

-


-

-

NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL
OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.



CONNECTOR
WITHOUT FLANGE TYPE




CONNECTOR
WITH FLANGE TYPE

MATING CONDITION (REFERENCE)
(SCALE 2:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
單位：耗
mm



MATERIAL
材料

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ± 0.2
1 PLC ± 0.2
2 PLC ± 0.2
3 PLC ± 0.2
4 PLC ± 0.2
ANGLES ± 0.2

FINISH
仕上

DWN

CHK

APVD

PRODUCT SPEC

製品規格

APPLICATION SPEC

取付適用規格

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME
名称

HDMI 19 POS
RECEPTACLE ASSY SMT TYPE
-LEAD FREE-

SIZE

CAGE CODE

DRAWING NO
番号

RESTRICTED TO

A3

00779

C-1747981

SCALE
尺度 2:1

SHEET
8 OF 8

REV
F4