


LOC	DIST	P	LTR	DESCRIPTION	DATE	OWN	APVD
CE	16	AF	REV PER	0A00-0060-03	07MAR03	DDE	SB



1. DIMENSIONS IN [] ARE IN INCHES.
2. INSTRUCTION SHEET 408-9645.
- 3** BODY: ELECTROLESS NICKEL
COUPLING NUT: ELECTROLESS NICKEL
- 4** BODY: BRASS
CAPILLARY: ZIRCONIUM OXIDE (ZrO₂)
COUPLING NUT: ZINC
STRAIN RELIEF: THERMOPLASTIC
- 5** BULK PACKAGED
- 6** SHORT BOOT
- 7** CLEAR TUBING USED ONLY ON 900μm BUFFERED FIBER WITHOUT STRENGTH MEMBERS.
- 8** BARE BUFFER (900μm) BOOT
- 9** PVC TUBING NOT INCLUDED
- 10** LONG STRAIN RELIEF AND BARE BUFFER BOOT

9	OBSOLETE	BLACK	8		125±2 μm	2-501380-1
5	OBSOLETE	BLACK	6		125±2 μm	2-501380-0
5	OBSOLETE	BEIGE	6		125±2 μm	1-501380-9
5	OBSOLETE	BLACK		GREEN	140±3 μm	1-501380-8
5	OBSOLETE	BLACK			125±2 μm	1-501380-7
		BLACK	6		125±2 μm	1-501380-6
5	OBSOLETE	BLACK	6		125±2 μm	1-501380-5
5	OBSOLETE	BLACK	6		125±2 μm	1-501380-4
	OBSOLETE	BEIGE	6		125±2 μm	1-501380-3
	OBSOLETE	BEIGE	6	GREEN	140±3 μm	1-501380-2
		BLUE	6		125±2 μm	1-501380-1
	OBSOLETE	BEIGE	6	GREEN	140±3 μm	1-501380-0
5		BLUE	6		125±2 μm	501380-9
	OBSOLETE	RED		GREEN	140±3 μm	501380-8
	OBSOLETE	RED			125±2 μm	501380-7
		BLACK		GREEN	140±3 μm	501380-6
	OBSOLETE	BLACK			125±2 μm	501380-5
	OBSOLETE	BEIGE		GREEN	140±3 μm	501380-4
	OBSOLETE	BEIGE			125±2 μm	501380-3
	OBSOLETE	BLACK		GREEN	140±3 μm	501380-2
10		BLACK			125±2 μm	501380-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN C. EISENHOUR 5-3-88	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK A. PLOTTS 5-4-88	AMP CONNECTOR KIT, 2.5mm BAYONET, OPTIMATE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		APVD E. MONROE 5-4-88	NAME	
MATERIAL 4		PRODUCT SPEC 108-1492	SIZE A2	
WEIGHT		APPLICATION SPEC	CAGE CODE (DRAWING NO) 00779	
CUSTOMER DRAWING		RESTRICTED TO	SCALE 2:1	
		REV	SHEET 1 OF 1	
		AF		