

EDAC PART NO. SYSTEM

A20-108-261-210

- SERIES _____
- NO. OF PORTS _____
- TOTAL NO. OF CONTACTS _____
- AA=128 (DUAL 8 PORTS)
- CONTACT PLATING _____
- 2 - GOLD FLASH
- 3 - 15 MICRONS OF GOLD
- 6 - 30 MICRONS OF GOLD
- 9 - 50MICRONS OF GOLD
- CONTACT TAIL TYPE _____
- * 2 - VERTICAL
- 6 - R/RANGE
- * 9 - SURFACE MOUNT
- SMT ONLY AVAIL.
- IN SINGLE PORT
- * CONTACT EDAC INC. FOR AVAILABILITY
- 0 - SINGLE ROW OF PORTS
- 1 - TWO ROWS OF PORTS
- 0 - NO SHIELD
- 1 - METAL SHIELD
- RIGHT LED COLOR
- 0 - BLANK
- 1 - YELLOW
- 2 - RED
- 3 - GREEN
- 4 - BI-COLOR (1-GREEN/2-YELLOW)
- 5 - BI-COLOR (1-RED/2-GREEN)
- 6 - BI-COLOR (1-GREEN/2-ORANGE)
- 7 - BI-COLOR (1-RED/2-YELLOW)
- 8 - ORANGE
- LEFT LED COLOR
- 0 - BLANK
- 1 - YELLOW
- 2 - RED
- 3 - GREEN
- 4 - BI-COLOR (1-GREEN/2-YELLOW)
- 5 - BI-COLOR (1-RED/2-GREEN)
- 6 - BI-COLOR (1-GREEN/2-ORANGE)
- 7 - BI-COLOR (1-RED/2-YELLOW)
- 8 - ORANGE
- TYP. FOR BI-COLORS
- LED'S
- GREEN
- YELLOW
- RED
- GREEN
- ORANGE
- RED
- YELLOW




THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR ROHS COMPLIANCY.

MODULAR JACKS WITH LED'S
PART NUMBER STRUCTURE


EDAC INC
TORONTO, ONTARIO
CANADA
YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC. AND
SHALL NOT BE REPRODUCED OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.


THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER
ORIGINAL ①



CODE: 0 - NO SHIELD



CODE: 1 - SHIELD

ACAD REFERENCE NO. A20-000-SALES

DRAWN: R.BLAKEY DATE: JAN 27/06

PART NUMBER

A20-000-000

DRAWING NUMBER

A20-000-000

ISSUE

1