



DIMENSIONS:

A	2.500" ±0.063
B	3.150" ±0.125
C	3.256" ±0.063
D	2.000" ±0.063
E	2.150" ±0.063
F	2.650" ±0.063
G	0.188" x 0.375" ±0.015



NOTE: ALL LEADS 11" MIN. OUT.



ELECTRICAL DATA:

TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
I _{ex}	@ 240V, 60Hz, BRN - BLU	3.5mA	Max.
Sec. N.L.V	@ 240V, 60Hz, BRN - BLU		
	BRN - RED = RED - BLU =	120.0V	±2%
	BLK - GRN/YEL =	7.626V	±2%
	BLK - GRN =	10.77V	±2%
Polarity	BRN, BLK	IN PHASE	
DCR	@ 20°C, BRN - RED =	82.00 Ω	±20%
	@ 20°C, RED - BLU =	108.3 Ω	±20%
	@ 20°C, BLK - GRN/YEL =	0.253 Ω	±20%
	@ 20°C, BLK - GRN =	0.462 Ω	±20%
HIPOT	PRIMARY - SECONDARY	2000V, 60Hz, 1 SEC	

REV.#	REVISION	DATE	HAMMOND MANUFACTURING™ ELECTRONIC DIVISION 52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5 PH # (519) 886-6181 FAX # (519) 886-9540			
0	RELEASED.	02/22/11				
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: 1750JA TRANSFORMER	DWG. NO. 1750JA
			DATE: 02/22/11	APP'D. BY: DIMENSIONS: IN(X) MM()		