

LOC	DIST	REVISIONS					
AD	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H4	PART STATUS UPDATED IN THE PARTS LIST TABLE	27AUG2015	KJK	PS

D

C

B


A

D

C


B

A



NOTES:

- POINT OF MEASUREMENT FOR PLATING THICKNESS
- THE TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD



3.984	3.900	39	80	4-87227-0	
3.884	3.800	38	78	3-	-9
3.784	3.700	37	76	3-	-8
3.684	3.600	36	74	3-	-7
3.584	3.500	35	72	3-	-6
3.484	3.400	34	70	3-	-5
3.384	3.300	33	68	3-	-4
3.284	3.200	32	66	3-	-3
3.184	3.100	31	64	3-	-2
3.084	3.000	30	62	3-	-1
2.984	2.900	29	60	3-	-0
2.884	2.800	28	58	2-	-9
2.784	2.700	27	56	2-	-8
2.684	2.600	26	54	2-	-7
2.584	2.500	25	52	2-	-6
2.484	2.400	24	50	2-	-5
2.384	2.300	23	48	2-	-4
2.284	2.200	22	46	2-	-3
2.184	2.100	21	44	2-	-2
2.081	2.000	20	42	2	-1
1.984	1.900	19	40	2-	-0
1.884	1.800	18	38	1-	-9
1.784	1.700	17	36	1-	-8
1.684	1.600	16	34	1-	-7
1.584	1.500	15	32	1-	-6
1.484	1.400	14	30	1-	-5
1.384	1.300	13	28	1-	-4
1.284	1.200	12	26	1-	-3
1.184	1.100	11	24	1-	-2
1.084	1.000	10	22	1-	-1
.984	.900	9	20	1-	-0
.884	.800	8	18		-9
.784	.700	7	16		-8
.684	.600	6	14		-7
.584	.500	5	12		-6
.484	.400	4	10		-5
.384	.300	3	8		-4
.284	.200	2	6		-3
.184	.100	1	4		-2
.084	—	—	2	87227-1	
C	B	A	NO OF POS	ASSEMBLY PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	5-15-85	TE Connectivity		
		CHK	5-21-85			
DIMENSIONS: INCHES		APVD	5-21-85	NAME		
		PRODUCT SPEC	—			
		APPLICATION SPEC	—	ASSEMBLY, MOD II, HEADER, DOUBLE ROW, .100 X .100 CL. VERTICAL, .025 SQUARE POSTS		
MATERIAL		WEIGHT	—	SIZE	CAGE CODE	DRAWING NO
HOUSING-FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK				A2	00779	C=87227
POSTS-PHOS BRONZE				CUSTOMER DRAWING		
				SCALE	4:1	SHEET 1 of 1
						REV H4