

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026192061

Status:

Active

Overview:

KK®

Description:

3.96mm (.156") Pitch KK® Wire-to-Board Header, Vertical, Round Pin, with Polarizing Wall, 6 Circuits, Tin (Sn) Plating

Documents:

3D Model

Drawing (PDF)

Product Specification PS-99020-0087 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Overview

Product Name

PCB Headers

3190

Wire-to-Board

KK®

KK®

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

Orientation

PC Tail Length (in)

PC Tail Length (mm)

PCB Locator

PCB Retention

PCB Thickness Recommended (in)

PCB Thickness Recommended (mm)

Packaging Type

Pitch - Mating Interface (in)

Pitch - Mating Interface (mm)

Plating min: Mating (µin)

Plating min: Mating (µm)

Plating min: Termination (µin)

Plating min: Termination (µm)

Polarized to PCB

Shrouded

Stackable

Temperature Range - Operating

Termination Interface: Style

No

6

6

Natural

25

No

94V-2

No

No

None

None

Brass

Tin

Tin

Nylon

1

Vertical

0.175 In

4.45 mm

No

None

0.062 In

1.60 mm

Bag

0.156 In

3.96 mm

200

5

200

5

No

Partial

No


0°C to +75°C

Through Hole

Electrical

CSA

LR19980



Series
image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

3190Series

Mates With

3069 KK® Crimp Terminal Housing. 3215 KK® PC Board Connector

Current - Maximum	7A
TUV	R72090224
Voltage - Maximum	250V
Solder Process Data	
Lead-free Process Capability	Wave Capable (TH only)
Material Info	
Old Part Number	319006A
Reference - Drawing Numbers	
Product Specification	PS-99020-0087
Sales Drawing	SDAE-3190-N**

This document was generated on 02/04/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION