

UNLESS OTHERWISE NOTED		TITLE:	DWG NO:
DIMENSIONS ARE IN INCHES	TOLERANCES ARE:		
ONE PLACE DECIMALS: ±	THREE PLACE DECIMALS: ±	HLT ASSEMBLY	HLT-XXXX-X-X
TWO PLACE DECIMALS: ±	FOUR PLACE DECIMALS: ±		
		ANGLES	
		±	
			SHEET 1 OF 1

HLT-XXXX-X-X

ROW SPECIFICATION
 (SEE FIG. 1)
 EXPRESSED IN NO. OF ROWS
 1 THRU 20

TERMINAL SPECIFICATION
 (SEE TABLE 1)

PLATING SPECIFICATION
 -G: GOLD, SPECIFY -G IN TERMINAL SUFFIX -X
 -T: TIN, SPECIFY -T IN TERMINAL SUFFIX -X

BODY LENGTH SPECIFICATION
 (SEE FIG. 1)
 EXPRESSED IN NO. OF POS. PER ROW
 1 THRU 20

- NOTES:
- 1.) FILL ALL POSITIONS.
 - 2.) PINS TO ENTER BODY FROM C'BORE SIDE.
 - 3.) BARB ON SOCKET MUST BE VISABLE BELOW BODY.

ASSEMBLY INSTRUCTIONS

DO NOT SCALE
FROM THIS PRINT





FIGURE 1



TERMINALS TO BE RECESSED (COUNTER-SUNK)
INTO BODY TO ALLOW BARB
PROTRUSION AT BOTTOM

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

MATERIAL:
PET POLYESTER
COLOR: BLACK

TERMINAL:
PHOS BRONZE

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MISC\MKTG
HLT-MKT

MADE BY: JORDAN 5-29-85
CHECKED BY: THRUSTON 6-4-85

ENGINEER
APPROVAL
BET
6-4-81

HLT-XXXX-X-X
SHEET 1 OF 1