


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		G	EC 0G3C 0808 04	15JAN05	BSV	RB
			G1	REVISED PER ECO-09-021826	03SEP09	KK	AEG



1

DATE CODE AND PART NUMBER ARE MARKED IN APPROXIMATE LOCATION SHOWN.

2

THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY, NOT TO CONTACT LOCATIONS

3

TOLERANCE IS NON-CUMULATIVE

4

DUPLEX PLATED: .000030 GOLD ON CONTACT AREA ONLY, .000150-.000300 BRIGHT TIN-LEAD ON SOLDER LEADS, ALL OVER .000050 MIN NICKEL.

5

POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE CONTACT BEAMS)

6

HSG: FLAME RETARDANT POLYESTER PCT, COLOR:BLACK

7

CONTACT: PHOS. BRONZE

8

TYCO LOGO AND CSA LOGO ARE MOLDED INTO HOUSING.

9

DUPLEX PLATED: .000030 GOLD ON CONTACT AREA ONLY, .000150-.000300 MATTE TIN ON SOLDER LEADS, ALL OVER .000050 MIN NICKEL.

10

ROHS 2002 /95/EC COMPLIANT.

11

NO PART NUMBER MARKING REQUIRED ON THIS PART.

12

2 POSITION PART HAS THE DATE CODE OPPOSITE OF TYCO LOGO.

13

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

RECOMMENDED PCB LAYOUT

13

4

35.56

37.97

[1.400]

[1.495]

13

4

27.94

30.35

[1.100]

[1.195]

13

4

99.06

101.47

[3.900]

[3.995]

13

4

73.66

76.07

[2.900]

[2.995]

13

4

48.26

50.67

[1.900]

[1.995]

13

4

22.86

25.27

[.900]

[.995]

11

4

10.16

12.57

[.400]

[.495]

13

12

11

4

-

2.41

-

[.095]

FINISH

B

A

NO OF POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

6

7

DWN
J KNAUB
12-12-94

CHK
A GABANY
12-12-94

APVD
A GABANY
12-12-94

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

Tyco Electronics

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME

ASSEMBLY, MOD IV, DBL ROW, .100 X .100
VERTICAL MOUNTED, CLOSED ENTRY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C-146219

-

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 1

REV G1