




DATE	DESCRIPTION	REV.
8.13.99	CHANGE AS PER ECN 99-057	A
8.08.05	CHANGE AS PER ECN 05-032	B
7.16.08	CHANGE AS PER ECN08-129	C
12.16.09	CHANGE AS PER ECN 09-188	D
12.28.15	CHANGE AS PER ECN 15-149	E
6.21.17	CHANGE AS PER ECN 17-044	F



Notes:

Shell: Mat'l: Steel,
Finish: Nickel plate, over Copper
Insulator: Mat'l- Glass Filled LCP
Contacts: Mat'l: Copper Alloy
Finish: Contact Area -Gold Plate over Nickel Plate
Solder Tail - Tin Plate over Nickel Plate

Electrical Specifications
Rated Voltage: 30V AC (rms)
Contact Current Rating: 1A Max.
Contact Resistance: 30 milliohms Max.
Dielectric Withstanding: 750V AC
Operating Temperature: -55°C to 85°C



ACTUAL SIZE

THIS DOCUMENT IS THE PROPERTY OF KEYSTONE ELECTRONICS CORP. AND SHALL NOT BE REPRODUCED, DISTRIBUTED OR USED AS A BASIS FOR MANUFACTURE WITHOUT PRIOR WRITTEN PERMISSION FROM KEYSTONE ELECTRONICS CORP.

KEYSTONE ELECTRONICS CORP.			
www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900			
PART NAME			
USB A-TYPE DUAL-HORIZONTAL SOCKET			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		NT	6.18.98
TOLERANCES		CODE	DWG NO.
DECIMAL $\pm .010$ [± 0.25]		C	922
ANGULAR $\pm 1^\circ$			
UNLESS OTHERWISE SPECIFIED			