


SP series

Washable snap-action pushbutton switches

Distinctive features and specifications



Process sealed

- Secure assembly of the two case parts
- Internally sealed bushing
- Epoxy sealed terminals

Process compatible (plain bushing models)

- Wave solderable
- Washable

B2

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - gold plated brass contacts : 100mA 30VDC
 - silver or gold plated silver contacts : 1A 30VDC
- Initial contact resistance : 50 mΩ max.
- Insulation resistance : 1.000 MΩ min.
- Dielectric strength : 1.000 Vrms 50 Hz min.
- Electrical life : 60.000 cycles

MATERIALS

- Case and cover : UL94-V0, polyamide, glass filled or PES
- Actuator : polyamide, glass filled
- Contacts
 - 0 : brass, gold plated
 - 1 : silver
 - 2 : silver, gold plated
- Terminal seal : epoxy

GENERAL SPECIFICATIONS

- Torque : 0,25 Nm (.18 Ft.lb) applied to nut (threaded bushing)
- Total travel : 0,50 mm (.019)
- Mechanical strength :
Terminals are strengthened by a bracket or a ground plate ensuring the rigidity of the switch on the board. Actuator strength is 10N max.
- Operating temperature : -20°C to +85°C
- Storage temperature : -40°C to +85°C
- Moisture :
The insulating materials employed and the complete seal permit the switches to withstand a 56 days moisture test (IEC 68-2-3).
- Soldering - thermal shock (plain bushing models) :
The switches are especially designed for flow soldering at 260°C during 5 seconds owing to high temperature polymer parts.
- Iron soldering (threaded bushing models) : 300°C max., 5 seconds max.
- Solderability : The switches are tested at 235°C according to IEC 68-2-20 after accelerated aging.

AGENCY APPROVAL





Availability : all models with silver or gold plated silver contacts.

Marking : to order switches marked UL, complete appropriate box of ordering format.

SP series

Washable snap-action pushbutton switches

Overview



ABOUT THIS SERIES

On the following pages, you will find successively :

- model structure of switches
- options in the same order as above
- Specifications are on previous page.

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



Mounting accessories : standard hardware supplied with all models with Ø 6,35 (1/4) threaded bushing :
2 hex nuts 8 mm (.314) across flats, 1 locking ring and 1 lockwasher.
Standard and special hardware available are presented in section I.




Packaging unit : 25 or 50 pieces depending on model.

SP series



Washable snap-action pushbutton switches

MODEL
STRUCTURE


Plain or threaded bushing



- Solder lug, straight PC or right angle terminals
- Features of threaded bushing models :
 - max. torque : 0,25 Nm (.18 Ft.lb)
 - iron soldering : 300°C max., 5 seconds max.
- 1 and 2 pole configurations



MODEL STRUCTURE



Shown with standard plunger

B2

Plain bushing - straight PC terminals




Single pole

SP35P0... 00

Double pole

SP45P0... 00



Plain bushing - bracket mounting




Single pole

SP35Y0... 00

Double pole

SP45Y0... 00



Plain bushing - right angle terminals - horizontal





Single pole

SP35W0... 00

Double pole

SP45W0... 00





SP series

Washable snap-action pushbutton switches

Plain or threaded bushing

Shown with standard plunger

Plain bushing - right angle terminals - vertical




Single pole

SP35WW... 00

Double pole

SP45WW... 00




Threaded bushing - solder lug terminals



Single pole

SP35S0... 77




Threaded bushing - straight PC terminals




Single pole

SP35P0... 77




PANEL CUT-OUT




SP series

Washable snap-action pushbutton switches




CONTACT AND TERMINAL MATERIALS




0 Brass, gold plated
1 Silver
2 Silver, gold plated

B2


PLUNGERS




OPTIONS / AGENCY APPROVAL




00 Standard model
01 UL marking for standard model
02 UL marking for threaded bushing model (single pole models only)
76 Short plain bushing for 02 plunger (single pole models only)
77 Threaded bushing
(included in model numbers on previous page)




CAPS




Blank Without cap




P/N U2400





P/N U2510




P/N U2130



Standard - P/N U2900

P/N U3400
Not available with plunger 02

Square - P/N U910

Square - P/N U2340
Not available with plunger 02


Cap colours	
Replace last "0" by number	
1	blue
1/4	dark blue
2	black
3	green
4	grey
5	yellow
6	red
7	ivory
7/1	white
9	orange

To order caps separately, use their P/N (U...) (for threaded bushing order only separately).


DRESS NUTS

Chrome plated


For threaded bushing models only.



For cap U2510



For cap U3400



For cap U2900

Dress nuts are to be ordered separately.