

ADAPTERS, BETWEEN-SERIES

2.4mm / 2.9mm , DC - 40 GHz

SPECIFICATIONS:

Models: 5151, 5152, 5153, 5154

RoHS
Compliant

AEROFLEX
A passion for performance.

Electrical:

Frequency Range _____ DC - 40 GHz
VSWR _____

DC - 18 GHz _____ 1.10:1 Max.

18 - 26.5 GHz _____ 1.20:1 Max.

26.5 - 40 GHz _____ 1.30:1 Max.

Impedance _____ 50 Ohms

Operating Temp. Range _____ -65°C to +125°C

Mechanical:

2.4mm Connectors _____ Passivated Stainless Steel

Mates with MIL-STD-348


2.9mm Connectors _____ Passivated Stainless Steel

Mates both Mechanically and Electrically with
SMA, 3.5mm and K* Series Connectors


Conductors _____ Gold Plated Beryllium Copper

* K is a Trademark of Anritsu Corp.


Model Number: **5154**
2.4mm Male / 2.9mm Male




Model Number: **5153**
2.4mm Male / 2.9mm Female



Model Number: **5152**
2.4mm Female / 2.9mm Male



Model Number: **5151**
2.4mm Female / 2.9mm Female



Note: Dimensions in Brackets are Expressed in Millimeters and are for Reference Only.

5154: REV C

AEROFLEX
INMET

Aeroflex / Inmet, Inc. • 300 Dino Drive, Ann Arbor, MI 48103 • U.S.A.
888-244-6638 or 734-426-5553 • FAX: 734-426-5557
www.aeroflex.com/inmet • inmet@aeroflex.com