






PANEL THICKNESS	X
0.75-1.25	19.2 -0.1
1.25-2.0	19.4 -0.1
2.0-3.0	19.8 -0.1



PANEL CUTOOUT



CIRCUIT: SPDT

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
DN	NONE	DN
1a-1	DPEN	1-1b

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY.
4. RATING: 15A @ 125VAC OR 6A @ 250VAC
5. MECHANICAL LIFE: 15,000 cycles
6. ELECTRICAL LIFE: 10,000 cycles
7. INSULATION RESISTANCE: $>1000 \text{ Mega } \Omega$
8. CONTACT RESISTANCE: $<20 \text{ Mega } \Omega$
9. DIELECTRIC STRENGTH: $>1500 \text{ V } 1 \text{ minute}$
 $>3000 \text{ V between poles}$



					TITLE
B	11502	REVISED AND REDRAWN	5/21/01	CJB	R1966C BLK BLK E S
REV.	ECN No.	DESCRIPTION	DATE	CHKD	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					
SCALE		DATE	DR	DWG	REV
1.5:1		12/06/00	PML	M302201	B