




SPECIFICATIONS

Ratings:	1A @ 120 VAC
Electrical Life:	50,000 cycles typical
Contact Resistance:	10mΩ max. typical @ 2-4 VDC 100mA for both silver and gold plated contacts.
Insulation Resistance:	1,000MΩ min.
Dielectric Strength:	1,000 V rms @ sea level.
Operating Force:	200 ± 50 gf

MATERIALS

Case:	Diallyl Phthalate (DAP)
Plunger:	Glass filled nylon or glass filled polyester
Bushing:	Nickel plated brass
Housing:	Stainless steel
Contacts:	Silver or Gold plated copper alloy.





EXAMPLE

800A → WSP9 → M7 → R → E




Model No.	TYPE
WSP8	ON (ON)
WSP9	OFF (ON)

Schematic () = Momentary




P.C. MOUNTING




TERMINATION OPTIONS

M2 P.C. Mounting






SEALED SUB-MINIATURE PUSHBUTTON SWITCHES

TERMINATION CONTINUED




M6

SPST






P.C. MOUNTING





M6-1

SPST






P.C. MOUNTING




M7

SPST





P.C. MOUNTING




VS-2

SPST



P.C. MOUNTING



CONTACT MATERIAL OPTIONS

Q

Fixed Terminal: Silver plated copper alloy.
Moving Contacts Silver plated copper alloy.
Rating: 1 AMP @ 120VAC or 28 VDC.

R

Fixed Terminal: Copper alloy with gold plate over nickel plate.
Moving Contact: Copper alloy with gold plate over nickel plate.
Rating: 0.4 VA max. @ 20 VAC or DC max.

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.