

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

— ,4:1 .



COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR

DESCRIPTION

DATE

DWN

APVD

B1






REVISED (ECR-13-009702)

7MAY13

S.H

V.P

1. EU ROHS-RELATED RESTRICTED SUBSTANCE SPEC IN HOMOGENEOUS MATERIAL REFER TO TEC-138-702 REV.G:
LEAD < 1000PPM, CADMIUM < 100PPM, MERCURY < 1000PPM
CHROMIUM VI < 1000PPM, PBB <1000PPM, PBDE < 1000PPM
2. HALOGEN FREE SPEC:
CHLORINE (Cl): 900 ppm MAX.
BROMINE (Br): 900 ppm MAX.
CHLORINE (Cl) + BROMINE (Br): 1500 ppm MAX.



A'SSY P/N				
	1-2129458-2	1-2129458-1	2129458-2	2129458-1
DIM B	1.2	1.4	1.2	1.4
DIM A	1.2	1.4	1.2	1.4

Q'TY

1	1			0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.00127mm MIN. NICKEL UNDERPLATED ALL OVER	COPPER ALLOY	GROUND SHELL	⑤
2	2	2	2	0.0002mm GOLD PLATING ON CONTACT AREA, 0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.002mm MIN. NICKEL UNDERPLATED ALL OVER	COPPER ALLOY	POWER CONTACT	④
1	1			0.0002mm GOLD PLATING ON CONTACT AREA, 0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.002mm MIN. NICKEL UNDERPLATED ALL OVER	COPPER ALLOY	DETECT CONTACT	③
2	2	2	2	0.0002mm GOLD PLATING ON CONTACT AREA, 0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.002mm MIN. NICKEL UNDERPLATED ALL OVER	COPPER ALLOY	GROUND CONTACT	②
1	1			BLACK	HIGH TEMPERATURE THERMO-PLASTIC (UL94V-0)	HOUSING	①
FINISH/COLOR					MATERIAL	PART NAME	NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	mm
MATERIAL	SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0-PLC	±
1-PLC	±
2-PLC	±
3-PLC	±
4-PLC	±
ANGLES	±
FINISH	

DWN	S.HUANG	20JUN2012
CHK	V.PENG	20JUN2012
APVD	W.KODAMA	20JUN2012
PRODUCT SPEC	108-99040	
APPLICATION SPEC	501-99041	
WEIGHT	1.94g	
CUSTOMER DRAWING		

TE Connectivity			
NAME			
DC POWER JACK CONNECTOR DIP TYPE (10.7A)			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2129458	
SCALE		SHEET	REV
4:1		1 of 3	B1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.



COPYRIGHT - By -

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

-

-

-

D

D

C




C

B

B

A


A



DETAIL B

DETAIL A

PLUG OVERMOLD



MATING CONDITION

: CONNECTOR OUTER LINE (NO COMPONENT AREA)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC


APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm -$

1 PLC $\pm -$

2 PLC $\pm -$

3 PLC $\pm -$

4 PLC $\pm -$

ANGLES $\pm -$

FINISH $\pm -$

± 0.25

$\pm 3^\circ$

MATERIAL

FINISH



TE Connectivity

NAME

DC POWER JACK CONNECTOR
DIP TYPE (10.7A)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2129458

SCALE

5:1

SHEET

2 OF 3

REV

B1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

©

COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION


DATE

DWN

APVD



SEE SHEET 1

4. SHIPPING BOX DIMENSION: 445mmX445mmX270mm








USER DIRECTION

OF UNREELING



A-A

DETAIL F
SCALE: FREEDETAIL G
SCALE 10:1

450	5	2250
PCS/REEL	REEL/SHIPPING BOX	TOTAL Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity			
		CHK				
		APVD	NAME			
DIMENSIONS: mm		PRODUCT SPEC	DC POWER JACK CONNECTOR DIP TYPE (10.7A)			
		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT	A3	00779	C-2129458	
MATERIAL		CUSTOMER DRAWING	SCALE	NA	SHEET	REV
					3 of 3	B1