

BS107, BS107A

Preferred Device

Small Signal MOSFET 250 mAmps, 200 Volts N-Channel TO-92

Features

- AEC Qualified
- PPAP Capable
- Pb-Free Package is Available*

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	200	Vdc
Gate-Source Voltage	V_{GS}	± 20	Vdc
- Continuous	V_{GSM}	± 30	Vpk
- Non-repetitive ($t_p \leq 50 \mu s$)			
Drain Current	I_D	250	mAdc
Continuous (Note 1)	I_{DM}	500	
Pulsed (Note 2)			
Total Device Dissipation @ $T_A = 25^\circ C$ Derate above $25^\circ C$	P_D	350	mW
Operating and Storage Junction Temperature Range	T_J, T_{stg}	-55 to 150	$^\circ C$

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. The Power Dissipation of the package may result in a lower continuous drain current.
2. Pulse Test: Pulse Width $\leq 300 \mu s$, Duty Cycle $\leq 2.0\%$.




ON Semiconductor®

<http://onsemi.com>


250 mAmps, 200 Volts

$R_{DS(on)} = 14 \Omega$ (BS107)


$R_{DS(on)} = 6.4 \Omega$ (BS107A)



MARKING DIAGRAM



TO-92
CASE 29-11
STYLE 30



xxx = BS107 or BS107A
A = Assembly Location
Y = Year
WW = Work Week
▪ = Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping
BS107	TO-92	1000 Units/Box
BS107G	TO-92 (Pb-Free)	1000 Units/Box
BS107A	TO-92	1000 Units/Box
BS107AG	TO-92 (Pb-Free)	1000 Units/Box
BS107ARL1	TO-92	2000/Ammo Pack
BS107ARL1G	TO-92 (Pb-Free)	2000/Ammo Pack

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

Preferred devices are recommended choices for future use and best overall value.

BS107, BS107A

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Characteristic	Symbol	Min	Typ	Max	Unit
----------------	--------	-----	-----	-----	------

OFF CHARACTERISTICS

Zero-Gate-Voltage Drain Current ($V_{DS} = 130\text{ Vdc}$, $V_{GS} = 0$)	I_{DSS}	-	-	30	nAdc
Drain-Source Breakdown Voltage ($V_{GS} = 0$, $I_D = 100\text{ }\mu\text{Adc}$)	$V_{(BR)DSX}$	200	-	-	Vdc
Gate Reverse Current ($V_{GS} = 15\text{ Vdc}$, $V_{DS} = 0$)	I_{GSS}	-	0.01	10	nAdc

ON CHARACTERISTICS (Note 3)

Gate Threshold Voltage ($I_D = 1.0\text{ mAdc}$, $V_{DS} = V_{GS}$)	$V_{GS(Th)}$	1.0	-	3.0	Vdc
Static Drain-Source On Resistance BS107 ($V_{GS} = 2.6\text{ Vdc}$, $I_D = 20\text{ mAdc}$) ($V_{GS} = 10\text{ Vdc}$, $I_D = 200\text{ mAdc}$) BS107A ($V_{GS} = 10\text{ Vdc}$) ($I_D = 100\text{ mAdc}$) ($I_D = 250\text{ mAdc}$)	$r_{DS(on)}$	- - - -	- - 4.5 4.8	28 14 6.0 6.4	Ω

SMALL-SIGNAL CHARACTERISTICS

Input Capacitance ($V_{DS} = 25\text{ Vdc}$, $V_{GS} = 0$, $f = 1.0\text{ MHz}$)	C_{iss}	-	60	-	pF
Reverse Transfer Capacitance ($V_{DS} = 25\text{ Vdc}$, $V_{GS} = 0$, $f = 1.0\text{ MHz}$)	C_{rss}	-	6.0	-	pF
Output Capacitance ($V_{DS} = 25\text{ Vdc}$, $V_{GS} = 0$, $f = 1.0\text{ MHz}$)	C_{oss}	-	30	-	pF
Forward Transconductance ($V_{DS} = 25\text{ Vdc}$, $I_D = 250\text{ mAdc}$)	g_{fs}	200	400	-	mmhos

SWITCHING CHARACTERISTICS

Turn-On Time	t_{on}	-	6.0	15	ns
Turn-Off Time	t_{off}	-	12	15	ns

3. Pulse Test: Pulse Width $\leq 300\text{ }\mu\text{s}$, Duty Cycle $\leq 2.0\%$.

RESISTIVE SWITCHING




Figure 1. Switching Test Circuit




Figure 2. Switching Waveforms

BS107, BS107A




Figure 3. On Voltage versus Temperature




Figure 4. Capacitance Variation




Figure 5. Transfer Characteristic




Figure 6. Output Characteristic




Figure 7. Saturation Characteristic


BS107, BS107A

PACKAGE DIMENSIONS


TO-92 (TO-226)

CASE 29-11

ISSUE AM



STRAIGHT LEAD
BULK PACK



SECTION X-X

NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.175	0.205	4.45	5.20
B	0.170	0.210	4.32	5.33
C	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
E	0.045	0.055	1.15	1.39
F	0.095	0.105	2.42	2.66
G	0.015	0.020	0.39	0.50
H	0.500	---	12.70	---
I	0.250	---	6.35	---
J	0.080	0.105	2.04	2.66
K	---	0.100	---	2.54
L	0.115	---	2.93	---
M	0.135	---	3.43	---

STYLE 30:

1. DRAIN
2. GATE
3. SOURCE

ON Semiconductor and **ON** are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada

Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative