

MICRO SWITCH
a Honeywell Division

FED. MF6 CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-2RW8478-D5

REPLACES X72364-BZ

RELEASE NO. PR-10815

CHECK

15°

TIP FINISHED

.018 R TO 32

LEVER DETAIL

SCALE - 5:1

MOUNTING HOLE COUNTERSINK

90° X .225 SURFACE DIA (2)

CORROSION RESISTANT

STEEL LEVER

1.026 ± .015

.090 MAX PRETRAVEL

.44

.765 R REF

.790 ± .020

.680 ± .030

.140 ± .002

.172 DIA

.660 ± .030

1.000

.47

1.94

.687 ± .010

1.047 ± .015

OPERATING POSITION

.25

.140 ± .002 DIA HOLE

.250 WIDE X .032 THICK

"QUICK CONNECT" TERMINAL (3)

.19

REVISIONS

A	CO-77591
DAW 22 JUN 94	
B	CO78138
DLT 20 JUL 94	
C	CO93346
DLT 17 SEP 98	
D	CO-94212-L
DLM 8 FEB 00	

1

MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX. DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE - - - - - 4 OZ MAX

RELEASE FORCE - - - - - 1/2 OZ MIN

DIFFERENTIAL TRAVEL - - - .002-.010

OVERTRAVEL - - - - - .050 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

S P D T

L96 15A 125, 250 OR 480 VAC

1/8HP 125 VAC, 1/4HP 250 VAC

1/2A 125 VDC, 1/4A 250 VDC

L288

L299

L306

CE

16A 250V

T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ±

WEIGHT

FORMTEK

DRAWN

T M M 17 DEC 81

C E B

21 DEC 81

C E B

THIRD ANGLE PROJECTION

FORMTEK

DRAWN

T M M 17 DEC 81

C E B

21 DEC 81

C E B