






RECOMENDED HOLE LAYOUT
FOR BOTTOM ENTRY OR PASS
THROUGH APPLICATIONS

- ① TE CONNECTIVITY LOGO AND CSA LOGO ARE MOLDED INTO THE HOUSING.
- ② TOLERANCE NON-CUMULATIVE.
- ③ DUPLEX PLATED: 0.00076 (.000030) GOLD IN CONTACT AREA, .00381-.00762 (.000150-.000300) BRIGHT TIN-LEAD ON LEADS, ALL OVER 0.00127 (.000050) MIN NICKEL.
- ④ THESE DIMENSIONS PERTAIN TO CAVITY C/L'S ONLY, NOT TO CONTACT LOCATIONS.
- ⑤ NO PART NUMBER MARKING REQUIRED ON THIS PART NUMBER.
- ⑥ HOUSING: FLAME RETARDANT GLASS FILLED POLYESTER - BLACK.
CONTACTS: PHOS. BRONZE.
- ⑦ POINT OF CONTACT DIMENSION.
- ⑧ POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE CONTACT BEAMS).
- ⑨ DUPLEX PLATED: 0.00076 (.000030) GOLD DUPLEX IN CONTACT AREA, 0.00381-0.00762 (.000150-.000300) MATTE TIN ON LEADS, ALL OVER 0.00127 (.000050) MIN NICKEL.
- ⑩ ROHS 2002/95/EC COMPLIANT
- ⑪ PART NUMBER AND DATE CODE ARE MARKED IN APPROXIMATE LOCATION SHOWN.
- ⑫ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. BOLES 19-11-92 CHK T. KINSEY 19-11-92 APVD —		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		NAME ASSEMBLY, MOD II DOUBLE ROW, .100 X .100 C/L, VERTICAL MOUNTED, CLOSED ENTRY, SHORT PT. CONTACTS	
		PRODUCT SPEC 108-25026 APPLICATION SPEC 114-25018		SIZE A2	
MATERIAL 		WEIGHT —		CAGE CODE 00779	
FINISH 		DRAWING NO C-534236		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE	4:1
				SHEET	1 of 2
				REV	V2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOCAD

DIST00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

FINISH	A	B	NO OF POSN	PART NO.
5	9	1.300	1.200	26
9	4.000	3.900	80	9-534236-0
9	3.900	3.800	78	8-534236-9
9	3.800	3.700	76	8-534236-8
9	3.700	3.600	74	8-534236-7
9	3.600	3.500	72	8-534236-6
9	3.500	3.400	70	8-534236-5
9	3.400	3.300	68	8-534236-4
9	3.300	3.200	66	8-534236-3
9	3.200	3.100	64	8-534236-2
9	3.100	3.000	62	8-534236-1
9	3.000	2.900	60	8-534236-0
9	2.900	2.800	58	7-534236-9
9	2.800	2.700	56	7-534236-8
9	2.700	2.600	54	7-534236-7
9	2.600	2.500	52	7-534236-6
9	2.500	2.400	50	7-534236-5
9	2.400	2.300	48	7-534236-4
9	2.300	2.200	46	7-534236-3
9	2.200	2.100	44	7-534236-2
9	2.100	2.000	42	7-534236-1
9	2.000	1.900	40	7-534236-0
9	1.900	1.800	38	6-534236-9
9	1.800	1.700	36	6-534236-8
9	1.700	1.600	34	6-534236-7
9	1.600	1.500	32	6-534236-6
9	1.500	1.400	30	6-534236-5
9	1.400	1.300	28	6-534236-4
9	1.300	1.200	26	6-534236-3
9	1.200	1.100	24	6-534236-2
9	1.100	1.000	22	6-534236-1
9	1.000	.900	20	6-534236-0
9	.900	.800	18	5-534236-9
9	.800	.700	16	5-534236-8
9	.700	.600	14	5-534236-7
9	.600	.500	12	5-534236-6
5	9	.500	10	5-534236-5
5	9	.400	8	5-534236-4
5	9	.300	6	5-534236-3
5	9	.200	4	5-534236-2
5	9	.100	-	2
5	9	.100	-	2

FINISH	A	B	NO OF POSN	PART NO.
5	9	1.300	1.200	26
9	4.000	3.900	80	9-534236-0
9	3.900	3.800	78	8-534236-9
9	3.800	3.700	76	8-534236-8
9	3.700	3.600	74	8-534236-7
9	3.600	3.500	72	8-534236-6
9	3.500	3.400	70	8-534236-5
9	3.400	3.300	68	8-534236-4
9	3.300	3.200	66	8-534236-3
9	3.200	3.100	64	8-534236-2
9	3.100	3.000	62	8-534236-1
9	3.000	2.900	60	8-534236-0
9	2.900	2.800	58	7-534236-9
9	2.800	2.700	56	7-534236-8
9	2.700	2.600	54	7-534236-7
9	2.600	2.500	52	7-534236-6
9	2.500	2.400	50	7-534236-5
9	2.400	2.300	48	7-534236-4
9	2.300	2.200	46	7-534236-3
9	2.200	2.100	44	7-534236-2
9	2.100	2.000	42	7-534236-1
9	2.000	1.900	40	7-534236-0
9	1.900	1.800	38	6-534236-9
9	1.800	1.700	36	6-534236-8
9	1.700	1.600	34	6-534236-7
9	1.600	1.500	32	6-534236-6
9	1.500	1.400	30	6-534236-5
9	1.400	1.300	28	6-534236-4
9	1.300	1.200	26	6-534236-3
9	1.200	1.100	24	6-534236-2
9	1.100	1.000	22	6-534236-1
9	1.000	.900	20	6-534236-0
9	.900	.800	18	5-534236-9
9	.800	.700	16	5-534236-8
9	.700	.600	14	5-534236-7
9	.600	.500	12	5-534236-6
5	9	.500	10	5-534236-5
5	9	.400	8	5-534236-4
5	9	.300	6	5-534236-3
5	9	.200	4	5-534236-2
5	9	.100	-	2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

FINISH

MATERIAL

6

DWN R. BOLES 19-11-92

CHK T. KINSEY 19-11-92

APVD -

PRODUCT SPEC 108-25026

APPLICATION SPEC 114-25018

WEIGHT -

CUSTOMER DRAWING

NAME

ASSEMBLY, MOD II DOUBLE ROW,
.100 X .100 C/L, VERTICAL MOUNTED,
CLOSED ENTRY, SHORT PT. CONTACTS

SIZE A2

CAGE CODE 00779

DRAWING NO C=534236

RESTRICTED TO -

SCALE 4:1

SHEET 2 OF 2

REV V2

5

12

OBSOLETE

12

OBSOLETE

3

4.000

3.900

80

4-534236-0

3

3.900

3.800

78

3-534236-9

3

3.800

3.700

76

3-534236-8

3

3.700

3.600

74

3-534236-7

3

3.600

3.500

72

3-534236-6

3

3.500

3.400

70

3-534236-5

3

3.400

3.300

68

3-534236-4

3

3.300

3.200

66

3-534236-3

3

3.200

3.100

64

3-534236-2

12

3.100

3.000

62

3-534236-1

12

3.000

2.900

60

3-534236-0

12

2.900

2.800

58

2-534236-9

12

2.800

2.700

56

2-534236-8

12

2.700

2.600

54

2-534236-7

12

2.600

2.500

52

2-534236-6

12

2.500

2.400

50

2-534236-5

12

2.400

2.300

48

2-534236-4

12

2.300

2.200

46

2-534236-3

12

2.200

2.100

44

2-534236-2

12

2.100

2.000

42

2-534236-1

12

2.000

1.900

40

2-534236-0

12

1.900

1.800

38

1-534236-9

12

1.800

1.700

36

1-534236-8

3

1.700

1.600

34

1-534236-7

3

1.600

1.500

32

1-534236-6

3

1.500

1.400

30

1-534236-5

3

1.400

1.300

28

1-534236-4

3

1.300

1.200

26

1-534236-3

12

1.200

1.100

24

1-534236-2

12

1.100

1.000

22

1-534236-1

3

1.000

.900

20

1-534236-0

3

.900

.800

18

534236-9

3

.800

.700

16

534236-8

3

.700

.600

14

534236-7

3

.600

.500

12

534236-6

3

.500

.400

10

534236-5

3

.400

.300

8

534236-4

12

3

.300

.200

6

534236-3

12

3

.200

.100

4

534236-2

12

3

.100

-

2

534236-1

534236

B

534236

B

1471-9 (3/11)