

Cable gland - RC-Z2052 - 1604216

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, shielded: no, cable diameter range: 8 mm ... 12 mm

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 248129
GTIN	4046356248129
Weight per Piece (excluding packing)	30.700 g
Custom tariff number	74199990
Country of origin	Germany

Technical data

General

Conductor entry	8 mm ... 12 mm
Pg housing screw connection	Pg11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Cable gland - RC-Z2052 - 1604216

Classifications

eCl@ss

eCl@ss 4.0	27141200
eCl@ss 4.1	27260700
eCl@ss 5.0	27149100
eCl@ss 5.1	27260700
eCl@ss 6.0	27149100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000441
ETIM 5.0	EC000441
ETIM 6.0	EC000441
ETIM 7.0	EC000441

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	39121311
UNSPSC 18.0	39121311
UNSPSC 19.0	39121311
UNSPSC 20.0	39121311
UNSPSC 21.0	39121311

Approvals

Approvals

Approvals

EAC

Ex Approvals

Cable gland - RC-Z2052 - 1604216

Approvals

Approval details

EAC		B.01687
-----	---	---------