

## SPECIFICATION

**Material:** Boot: APM RUBRGLAS™ (transparent silicone rubber), conforms to A-A-59588, Class III Grade 50, Frame: steel, zinc plated with chromate finish. Screw: SEELSKREW® (self-sealing screws), stainless steel with silicone rubber O-ring.

**Temperature Range:** HEXSEAL: -94°F to +400°F

**Pressure Range:** Dust tight and splashproof.

**Operational Life:** 10,000 actuations (minimum).

**Shelf Life:** Excess of 25 years.

**Resistant to:** Salt spray, sunlight, ozone, weather, corona and most acids.


### Notes:

1. Mounting screws are supplied in lengths shown unless otherwise specified.

2. New sizes and types of RUBRGLAS-SEELS® are being added regularly. Please request other types and styles as required.

**Agency Recognition:** Front Panel mounted Circuit Breaker Boots are UL- listed to UL Std. 50, types 1,2,3,12,12K and 13.

Back-of-Panel mounted Circuit Breaker boots are UL-listed to UL Std. 50, type 1, Also meet CSA standards.



### NOTES:

ASSEMBLY CONSISTS OF 1 BOOT, MAT'L APM RUBRGLAS®, 1 FRAME  
MAT'L C.R.S. ZINC PLATED WITH CHROMATE FINISH, & 2#6-32 APM SEELSKREWS® LENGTH =3/8  
UNLESS OTHERWISE SPECIFIED

TOLERANCES: UNLESS OTHERWISE NOTED ±1/32

|                                                                         |                                                                                                                                                                                             |                                                                 |                |                         |         |          |
|-------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------|----------------|-------------------------|---------|----------|
| H                                                                       | RUBBER and FRAME MAT'L CHANGED, WALL THICKNESS TOL. 0.010 CHANGED TO 0.005, HOLE DIM. Ø0.147" CHANGED TO Ø0.149", DELETED TO "DESIGN TO MEET MIL-5423" and DELETED TO SEELSKREW INFORMATION |                                                                 |                |                         | S. GOK  | 05.04.09 |
| G                                                                       | CAD COMPUTER GENERATED                                                                                                                                                                      |                                                                 |                |                         |         | 11.13.02 |
| F                                                                       | CORRECTED RAME WAS 1 1/2" NICK                                                                                                                                                              |                                                                 |                |                         |         | 01.10.69 |
| REV.                                                                    | DESCRIPTION                                                                                                                                                                                 |                                                                 |                |                         |         | DATE     |
| MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION. | TITLE:                                                                                                                                                                                      | CIRCUIT BREAKER BOOT, TOGGLE, WIDE ANGLE, TRANSPARENT (1 POLES) | ENG.           |                         | M.M.    |          |
| MAT'L: RUBRGLASS ①<br>CONFORMS TO A-A-59588 CL III                      |                                                                                                                                                                                             |                                                                 | DWN.           |                         | J.P.    | 12.24.58 |
|                                                                         |                                                                                                                                                                                             |                                                                 | CHKD.          |                         | J.CELLA | 05.04.09 |
| FINISH: GRADE 50<br>TRANSPARENT                                         | APM-HEXSEAL CORPORATION                                                                                                                                                                     |                                                                 | SCALE<br>1 : 1 | DWG. NO.<br><br>HE-1040 |         |          |

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.  
THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[APM HEXSEAL:](#)

[HE-1040](#)