


NO	DESCRIPTION	DATE
①	BACKGROUND FORMAT UPDATED	10.26.02




NOTES: UNLESS OTHERWISE SPECIFIED

- 1. BODIES:BRASS PER JIS-C3604
- 2. CENTER CONTACT:BRASS PER JIS-C3604
- 3. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 4. PART TO BE CLEAN AND FREE OF BURRS

6	SHELL	BRASS	1	NICKEL 100μ" MIN.
5	WASHER	BRASS	1	NONE
4	INSULATION	TEFLON	1	NONE
3	CENTER CONTACT	BRASS	1	GOLD
2	INSULATION	TEFLON	1	NONE
1	BODY	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q' TY	FINISH

製圖	DRAWN	TOLERANCE		品名		25-01		日期	DATE	版次	REV.
		.X	±0.2	TITLE					05.19.93		
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.	25-0001				
		.XXX	±0.05		mm(in)						
認定	APPROVAL	.XXX	±0.05	比例	SCALE	 佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.					
		ANGLE	±5°		4:1						

NO	DESCRIPTION	DATE
⚠	BACKGROUND FORMAT UPDATED	10.26.02




NOTES: UNLESS OTHERWISE SPECIFIED

- 1. BODIES:BRASS PER JIS-C3604
- 2. CENTER CONTACT:BRASS PER JIS-C3604
- 3. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 4. CONNECTOR INTERFACE PER MIL-STD-348A
- 5. PART TO BE CLEAN AND FREE OF BURRS

8	SHELL	BRASS	1	NICKEL 100μ" MIN.
7	GASKET	SILICONE	1	RED
6	WASHER II	BRASS	1	NONE
5	WASHER I	BRASS	1	NICKEL 100μ" MIN.
4	INSULATION	TEFLON	1	NONE
3	CENTER CONTACT	BRASS	1	GOLD
2	INSULATION	TEFLON	1	NONE
1	BODY	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q' TY	FINISH

製圖	DRAWN	TOLERANCE		品名		25-03		日期	DATE	版次	REV.
		.X	±0.2	TITLE					05.20.93		A-1
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.		25-0003			
		.XXX	±0.05		mm(in)						
認定	APPROVAL	ANGLE	±5°	比例	SCALE	 佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.					
					4:1						

NO	DESCRIPTION	DATE
	REDUCE SPRING WASHER FROM 2 PCS TO 1 PCS	06.06.97
	BACKGROUND FORMAT UPDATED	10.26.02



NOTES: UNLESS OTHERWISE SPECIFIED


- 1. BODIES:BRASS PER JIS-C3604
- 2. CENTER CONTACT:BRASS PER JIS-C3604
- 3. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 4. CONNECTOR INTERFACE PER MIL-STD-348A
- 5. PART TO BE CLEAN AND FREE OF BURRS

10	WASHER	BRASS	1	NICKEL 100μ" MIN.
9	INSULATION	TEFLON	1	NONE
8	CENTER CONTACT	BRASS	1	GOLD
7	WASHER	BRASS	1	NICKEL 100μ" MIN.
6	SPRING WASHER	SK-5	1	NICKEL 100μ" MIN.
5	WASHER	BRASS	1	NICKEL 100μ" MIN.
4	GASKET	SILICONE	1	RED
3	INSULATION	TEFLON	1	NONE
2	BODY	BRASS	1	NICKEL 100μ" MIN.
1	SHELL	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q' TY	FINISH



製圖	DRAWN	TOLERANCE		品名		25-04 (50Ω)		日期	DATE	版次	REV.		
		.X	±0.2	TITLE					05.14.93	A-2			
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.	25-0004	 佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.					
		.XXX	±0.05		mm(in)								
認定	APPROVAL		ANGLE	比例	SCALE								
			±5°		4:1								

NO	DESCRIPTION	DATE
⚠	BACKGROUND FORMAT UPDATED	10.26.02




NOTES: UNLESS OTHERWISE SPECIFIED

- 1. BODIES:BRASS PER JIS-C3604
- 2. CENTER CONTACT:BRASS PER JIS-C3604
- 3. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 4. CONNECTOR INTERFACE PER MIL-STD-348A
- 5. PART TO BE CLEAN AND FREE OF BURRS

8	WASHER	BRASS	1	NICKEL 100μ" MIN.
7	INSULATION	TEFLON	1	NONE
6	CENTER CONTACT	BRASS	1	GOLD
5	WASHER	BRASS	1	NONE
4	BODY	BRASS	1	NICKEL 100μ" MIN.
3	GASKET	RUBBER	1	NONE
2	INSULATION	TEFLON	1	NONE
1	SHELL	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

製圖	DRAWN	TOLERANCE		品名		25-05		日期	DATE	版次	REV.
		.X	±0.2	TITLE					05.17.93		A-1
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.	25-0005				
		.XXX	±0.05		mm(in)						
認定	APPROVAL	ANGLE	±5°	比例	SCALE	 佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.					
					4:1						

NO	DESCRIPTION	DATE
⚠	USE STAINLESS STELL INSTEAD OF BRASS	05.15.95
△	BACKGROUND FORMAT UPDATED	10.26.02



NOTES: UNLESS OTHERWISE SPECIFIED

- 1. BODIES:BRASS PER JIS-C3604
- 2. CENTER CONTACT:BRASS PER JIS-C3604
- 3. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 4. CONNECTOR INTERFACE PER MIL-STD-348A
- 5. PART TO BE CLEAN AND FREE OF BURRS

8	BODY	BRASS	1	NICKEL 100μ" MIN.
7	WASHER	BRASS	1	NICKEL 100μ" MIN.
6	INSULATION	TEFLON	1	NONE
5	CENTER CONTACT	BRASS	1	GOLD
4	WASHER	STAINLESS STELL	1	NONE
3	GASKET	SILICONE	1	NONE
2	INSULATION	TEFLON	1	NONE
1	SHELL	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q' TY	FINISH




製圖	DRAWN	TOLERANCE		品名		25-06		日期	DATE	版次	REV.
		.X	±0.2	TITLE					05.18.93		A-2
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO. 25-0006			佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.		
		.XX	±0.1		mm(in)						
認定	APPROVAL	.XXX	±0.05	比例	SCALE						
		ANGLE	±5°		4:1						



佳楠精密電子股份有限公司
CHIN NAN PRECISION ELECTRONICS CO.,LTD.

NO	DESCRIPTION	DATE
①	BACKGROUND FORMAT UPDATED	10.26.02




NOTES: UNLESS OTHERWISE SPECIFIED

- 1. BODIES:BRASS PER JIS-C3604
- 2. CENTER CONTACT:BRASS PER JIS-C3604
- 3. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 4. PART TO BE CLEAN AND FREE OF BURRS

4	INSULATION	TEFLON	1	NONE
3	CENTER CONTACT	BRASS	1	GOLD
2	BODY	BRASS	1	NICKEL 100μ" MIN.
1	INSULATION	TEFLON	1	NONE
NO	DESCRIPTION	MATERIAL	Q' TY	FINISH

製圖	DRAWN	TOLERANCE		品名	25-07		日期	DATE	版次	REV.
		.X	±0.2	TITLE						
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO. 25-0007				
		.XXX	±0.05		mm(in)					
認定	APPROVAL	.XXX	±0.05	比例	SCALE	 佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.				
		ANGLE	±5°		4:1					

NO	DESCRIPTION	DATE
1	BACKGROUND FORMAT UPDATED	10.26.02




NOTES: UNLESS OTHERWISE SPECIFIED

- 1. BODIES:BRASS PER JIS-C3604
- 2. CENTER CONTACT:BRASS PER JIS-C3604
- 3. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 4. PART TO BE CLEAN AND FREE OF BURRS

5	WASHER	BRASS	1	NICKEL 100 μ" MIN.
4	INSULATION	TEFLON	1	NONE
3	BODY	BRASS	1	NICKEL 100 μ" MIN.
2	CENTER CONTACT	BRASS	1	GOLD
1	INSULATION	TEFLON	1	NONE
NO	DESCRIPTION	MATERIAL	Q' TY	FINISH

製圖	DRAWN	TOLERANCE		品名		25-08		日期	DATE	版次	REV.
		.X	±0.2	TITLE					05.19.93	A-1	A-1
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO. 25-0008			佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.		
		.XX	±0.1		mm(in)						
認定	APPROVAL	.XXX	±0.05	比例	SCALE						
		ANGLE	±5°		4:1						

NO	DESCRIPTION	DATE
1	BACKGROUND FORMAT UPDATED	10.26.02




NOTES: UNLESS OTHERWISE SPECIFIED

1. BODIES:BRASS PER JIS-C3604
2. CENTER CONTACT:BRASS PER JIS-C3604
3. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
4. CONNECTOR INTERFACE PER MIL-STD-348A
5. PART TO BE CLEAN AND FREE OF BURRS

5	WASHER	BRASS	1	NICKEL 100 μ " MIN.
4	INSULATION	TEFLON	1	NONE
3	CENTER CONTACT	BRASS	1	GOLD
2	INSULATION	TEFLON	1	NONE
1	BODY	BRASS	1	NICKEL 100 μ " MIN.
<i>NO</i>	<i>DESCRIPTION</i>	<i>MATERIAL</i>	<i>Q'TY</i>	<i>FINISH</i>

製圖	DRAWN	TOLERANCE		品名		25-09		日期	DATE	版次	REV.
		X	±0.2	TITLE					05.19.93		A-1
檢圖	CHECK	X	±0.1	單位	UNIT	DWG.NO.	25-0009				
		X	±0.1		mm(in)						
認定	APPROVAL	XXX	±0.05	比例	SCALE	 佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.					
		ANGLE	±5°		4:1						

NO	DESCRIPTION	DATE
①	BACKGROUND FORMAT UPDATED	10.26.02




NOTES: UNLESS OTHERWISE SPECIFIED

- 1. BODIES:BRASS PER JIS-C3604
- 2. CENTER CONTACT:BRASS PER JIS-C3604
- 3. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 4. CONNECTOR INTERFACE PER MIL-STD-348A
- 5. PART TO BE CLEAN AND FREE OF BURRS

5	WASHER	BRASS	1	NICKEL 100μ" MIN.
4	INSULATION	TEFLON	1	NONE
3	CENTER CONTACT	BRASS	1	GOLD
2	INSULATION	TEFLON	1	NONE
1	BODY	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q' TY	FINISH

製圖	DRAWN	TOLERANCE		品名		25-09		日期	DATE	版次	REV.
		.X	±0.2	TITLE					05.19.93		A-1
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.		25-0009			
		.XXX	±0.05		mm(in)						
認定	APPROVAL	.XXX	±0.05	比例	SCALE	佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.					
		ANGLE	±5°		4:1						

NO	DESCRIPTION	DATE
①	BACKGROUND FORMAT UPDATED	10.26.02




NOTES: UNLESS OTHERWISE SPECIFIED

- 1. BODIES:BRASS PER JIS-C3604
- 2. CENTER CONTACT:BRASS PER JIS-C3604
- 3. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 4. CONNECTOR INTERFACE PER MIL-STD-348A
- 5. PART TO BE CLEAN AND FREE OF BURRS

5	WASHER	BRASS	1	NICKEL 100μ" MIN.
4	INSULATION	TEFLON	1	NONE
3	BODY	BRASS	1	NICKEL 100μ" MIN.
2	CENTER CONTACT	BRASS	1	GOLD
1	INSULATION	TEFLON	1	NONE
NO	DESCRIPTION	MATERIAL	Q' TY	FINISH

製圖	DRAWN	TOLERANCE		品名		25-10		日期	DATE	版次	REV.
		.X	±0.2	TITLE					05.21.93		A-1
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.	25-0011		佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.		
		.XX	±0.1		mm(in)						
認定	APPROVAL	.XXX	±0.05	比例	SCALE						
		ANGLE	±5°		4:1						

NO	DESCRIPTION	DATE
①	BACKGROUND FORMAT UPDATED	10.28.02



NOTES: UNLESS OTHERWISE SPECIFIED

- 1. BODIES:BRASS PER JIS-C3604
- 2. CENTER CONTACT:BRASS PER JIS-C3604
- 3. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 4. PART TO BE CLEAN AND FREE OF BURRS

4	CENTER CONTACT	BRASS	1	GOLD
3	BODY	BRASS	1	NICKEL 100 μ" MIN.
2	INSULATION	TEFLON	1	NONE
1	SLEEVE	BRASS	1	NICKEL 100 μ" MIN.
NO	DESCRIPTION	MATERIAL	Q' TY	FINISH

製圖	DRAWN	TOLERANCE		品名		25-13		日期	DATE	版次	REV.
		.X	±0.2	TITLE					05.24.93		A-1
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.	25-0016				
		.XX	±0.1		mm(in)						
認定	APPROVAL	.XXX	±0.05	比例	SCALE	 佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.					
		ANGLE	±5°		4:1						