




FCIconnect.com



Copyright FCI



form: A3



PC card drilling dimensions(after plating)
(thickness 2.40±0.20mm)



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24B4GV00	D09P24B6GV00
15	39.14	33.32	25.18	25.12	19.18	D15P24B4GV00	D15P24B6GV00
25	53.03	47.04	39.12	38.84	33.12	D25P24B4GV00	D25P24B6GV00
37	69.32	63.50	55.68	55.30	49.68	D37P24B4GV00	D37P24B6GV00
						200 Mating cycles	500 Mating cycles

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24B4GV00LF	D09P24B6GV00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24B4GV00LF	D15P24B6GV00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24B4GV00LF	D25P24B6GV00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24B4GV00LF	D37P24B6GV00LF
						200 Mating cycles	500 Mating cycles

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

mat'l. code				surface	tolerance	projection	product family			
-				ISO 1302	ISO 406	ISO 1101	D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
H	ELX-I-18884	AB	2014/09/24	angles	linear					
				0°±2'	.0±0.1	MM	MALE CONNECTOR DELTA D ST			
					.00±0.1					
					.000±0.1	scale 2:1	straight,solder type			
				dr	LELEON	1992/09/14				
				engr	ALIAS BABU	2014/09/24	dwg no		sheet 1 of 1	size
				chr	MITHUN PAUL	2014/09/24	C01-8646-0107		A3	
				app	BIJU K PAUL	2014/09/24	type		Product Customer Drawing	
sheet index	revision	H								
	sheet	1								