









CIRCUIT DIAGRAM



MOLDED IN INTERNAL PCB
SHOWN FOR REFERENCE

3D VIEW
SCALE 3:2



5. MOTOROLA DIODE P/N: MUR460G.
PEAK REVERSE VOLTAGE = 600.0 V MAX.
PEAK FORWARD VOLTAGE = 1.28 V MAX.
AVERAGE FORWARD CURRENT = 4.0 A MAX.
CONSULT THE FACTORY FOR DETAILED SPECIFICATIONS.

4. TEMPERATURE RANGE: -55°C TO +125°C.
3. RECEPTACLE MATES WITH DT06-4S-****.
2. ALL DIMENSIONS UNLESS OTHERWISE SPECIFIED ARE $\pm .025$ [.63].

NOTES: 1. ALL DIMENSIONS ARE INCHES [METRIC].

REV
B DT04-4P-RT01

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. PI6233	10/11/99	WOODRUFF
A	REVISED PER E.O. PI6526	2/4/00	C. WOODRUFF
B	REVISED PER E.O. PI9626	4-21-08	ADD

SIGNATURE & DATE	
DR	J. APOSTOL 4FEB2000
CHK	R. Messer 4/11/00
PE	K. Kuster 6-27-07
APPD	S. Seund 6-28-07
SCALE	NONE WT

4 WAY RECEPTACLE
TERMINATOR
DT SERIES

ENVELOPE

EP	MATL. CODE
3850 INDUSTRIAL AVE. HEMET, CA 92545	
B DT04-4P-RT01	
DWG SIZE	CODE 11139 SHEET 1 OF 1