






LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION			DATE	APVD
CM	52					
	H	REV & REDWN PER EC 0L30-0096-97			2-28-97	RS

1. WIRE RANGE: 0.4 - 0.9 MM² (22 - 18 AWG)
2. INSULATION RANGE: 2.03 - 2.54



RECOMMENDED CUT OUT
FOR 1.57 MAX THICK PANEL



SECTION A-A SECTION B-B

1.30	.051	2.29	.090	3.43	.135	-	-
0.76	.030	2.16	.085	3.33	.131	13.89	.547
0.58	.023	2.03	.080	2.82	.111	13.64	.537
0.40	.016	1.78	.070	2.79	.110	12.24	.482
0.25	.010	1.75	.069	2.67	.105	5.72	.225
0.13	.005	1.57	.062	2.54	.100	5.08	.200
0.05	.002	1.55	.061	2.41	.095	4.06	.160
0.00	.000	1.40	.055	2.31	.091	3.81	.150
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL

0.40 BRASS

FINISH

MATTE TIN

DWN
T. BECK
2-28-97

CHK
R. SWING
2-28-97

APVD
A. BEDDICK
3-10-97

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

NAME
AMP Incorporated
Harrisburg, PA 17105-3608

SIZE
A2

CAGE CODE
00779

DRAWING NO
60704

RESTRICTED TO
-

SCALE
10:1

SHEET
1

OF
1

REV
H