

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0481471314
Status: Obsolete
Description: 2.50mm (.098") Pitch, Wire-to-Board, Through Hole, Right Angle, 13 Circuits Header, Lead-Free, Yellow

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
TUV	30683046
UL	E29179

General

Product Family	PCB Headers
Series	48147
Application	Signal, Wire-to-Board
Comments	Lead-free part
Product Name	N/A

Physical

Breakaway	No
Circuits (Loaded)	13
Circuits (maximum)	13
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.20mm (.126")
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Bag
Pitch - Mating Interface	2.50mm (.098")
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-25°C to +85°C
Termination Interface: Style	Through Hole - Kinked Pin


Electrical

Current - Maximum per Contact	3A
Voltage - Maximum	250V

Material Info

Reference - Drawing Numbers

Product Specification	PS-48104-001
Sales Drawing	SD-48147-001



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[48147Series](#)

Mates With

[48102](#) Wire-to-Board Crimp Terminal. [48103](#)
Wire-to-Board Crimp Housing

This document was generated on 05/10/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION