




CONDUCTOR DEPTH	28.45
	[1.12]
	MIN

OBSOLETE		6.73±0.13 [.265±.005]	1/4	BODY: COPPER ASTM-B187 ANNEALED TIN PL MIL-T-10727 0.00381[.000150] MIN THK INSERT & FUNNEL: BRASS ASTM B36 NICKEL PL SAE AMS QQ-N-290A, DATED JULY 2000, 0.00254 [.000100] MIN THK	—277150-4—
	34.0 ±3GRAMS	9.91±0.13 [.390±.005]	3/8		277150-3
	35.5 ±3GRAMS	8.33±0.13 [.328±.005]	5/16		277150-2
	36.0 ±3GRAMS	6.73±0.13 [.265±.005]	1/4		277150-1
	WEIGHT	‘A’	‘B’	MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 6/23/89	TE Connectivity				
DIMENSIONS: MM [INCHES]		CHK MS FEHER 10/16/90					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD AJ KAUFMAN 10/23/90	NAME				
		PRODUCT SPEC 108-11011	WIRE TERMINAL, RING TONGUE, SEALED COPALUM, 35.0mm [2] ALUMINUM 22.0mm [4] COPPER				
		APPLICATION SPEC 114-2134	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL SEE TABLE		FINISH SEE TABLE	WEIGHT SEE TABLE	A2	00779	C=277150	—
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV K		