

DO NOT
SCALE FROM
THIS PRINT

1. C REPRESENTS A CRITICAL DIMENSION.
2. MINIMUM PUSHOUT FORCE: .50 LBS.
3. COPLANARITY TO BE:
-DH: -36 THRU -28 POS: .008[0.20]
-02 THRU -27 POS: .006[0.15]
-SV, SH FULL STRIP STOCK: .008[0.20] (MUST MEET ASSEMBLY SPEC WHEN CUT.
4. PACKAGE IN TUBES PER SHT 4, TABLE 2. ALL OTHER POSITIONS BULK PACKAGE.
5. MAXIMUM CUT FLASH: .015[0.38].
6. NOTCH OF PPP-12 TO BE ORIENTED TOWARD SAME END AS POSITION 1.
7. ROWS TO BE WITHIN .004[0.10] OF ONE ANOTHER.
8. -36 MAX POSITION AVAILABLE, -50 FOR STOCK ONLY.
9. ENDWALL AFTER CUTTING: .033[0.84]±.005[0.13]
10. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.
11. FOR -SV TAIL STYLE: EVEN CUTS LOSE 2 POSITIONS PER CUT; ODD CUTS LOSE 1 POSITION PER CUT.
12. IF POLARIZATION OCCURS AT CENTER POSITION(S) OF BODY, MOVE PICK & PLACE PAD LEFT OR RIGHT TO NEXT AVAILABLE POSITION.
13. THIS DIMENSION IS TO BE MEASURED RELATIVE TO DATUM -Z-.

SSM-1XX-XXX-XX-XX-XX-X-XX-XX

No OF POSITIONS

-02 THRU -36
(SEE NOTE 8)

OPTION

-TR: TAPE AND REEL
(SEE FIG 8, SHT 4)
(29 POSITIONS MAX)

OPTION

-P: PICK AND PLACE PAD
(ONLY AVAILABLE ON -SV,
USE PPP-12, SEE FIG 6, SHT 3)
(SEE NOTE 12)

-K: POLYIMIDE FILM PAD
(SEE FIG 5, SHT 2)
(USE K-DOT-.138-.250-.005)
(NOT AVAILABLE ON -SH AND -DH)

POLARIZATION OPTION

-XX: POSITION TO BE POLARIZED
(USE PK-06-N, SEE FIG 7, SHT 3
FOR POLARIZATION POSITIONS)
(NOT AVAILABLE FOR -BE OPTION)

MOUNTING OPTION

-LC: LOCKING CLIP
(USE LC-05-TM, SEE NOTE 10)
(FOR -SH AND -DH USE MOLDED TO
POSITION BODIES)

OPTION

-BE: BOTTOM ENTRY
(ONLY AVAILABLE ON -SV)
(USE SSM-XX-S-BE)
(SEE FIG 2, SHT 2)

PLATING SPECIFICATION

-S: 30μ" SELECTIVE GOLD IN CONTACT
AREA, MATTE TIN ON TAIL.

-L: 10μ" SELECTIVE GOLD IN CONTACT
AREA, MATTE TIN ON TAIL.

-T: MATTE TIN ON CONTACT AND TAIL.

-F: 3μ" SELECTIVE GOLD IN CONTACT
AREA, MATTE TIN ON TAIL.

-STL: 30μ" SELECTIVE GOLD IN CONTACT
AREA, TIN/LEAD (90/10) ON TAIL.

-H: 30μ" SELECTIVE GOLD IN CONTACT
AREA, 3μ" SELECTIVE GOLD ON TAIL.

-LM: 10μ" SELECTIVE GOLD IN CONTACT
AREA, MATTE TIN ON TAIL.

-TM: MATTE TIN ON CONTACT AND TAIL.

-FM: 3μ" SELECTIVE GOLD IN CONTACT

TAIL SPECIFICATION

-SV: SINGLE VERTICAL (SEE FIG 1)
(USE SSM-XX-S)

-SH: SINGLE HORIZONTAL (SEE FIG 3, SHT 2)
(USE SSM-XX-SH)

-DH: DOUBLE HORIZONTAL (SEE FIG 4, SHT 3)
(USE BCH-XX-D)






FIG 1
-SV: SINGLE VERTICAL ROW
(SSM-1XX-XXX-SV-LC SHOWN)

TABLE 1		
BODY/LEAD STYLE	CONTACT #1	CONTACT #2
-SV	C-95-02-X	N/A
-SH	C-58-06-X	N/A
-DH	C-58-08-X	C-58-07-X



SECTION "A"-"A"

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES

.XX: ±.01 [0.3] 2°

.XXX: ±.005 [0.13]

.XXX: ±.0020 [0.051]

* PROPRIETARY NOTE *

THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 2:1

INSULATOR: LCP, UL 94 VO, COLOR: BLACK

CONTACT: PHOS BRONZE

DESCRIPTION:
.100[2.54] C.L. SURFACE MOUNT SOCKET STRIP

DWG. NO.

SSM-1XX-XXX-XX-XX-XX-X-XX-XX

BY: KOLB

09/11/1998

SHEET 1 OF 4




FIG 2

-SV-BE: SINGLE VERTICAL ROW BOTTOM ENTRY
(SSM-1XX-XXX-SV-BE SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)




FIG 5

-K: KAPTON PAD
(SSM-110-XXX-SV-K SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)
"R" = SEE FIG 1, SHEET 1 FOR OAL
"S" = "R"/2 - .0689 [1.750]







FIG 3

-SH: SINGLE HORIZONTAL
(SSM-136-XXX-SH-LC SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)



-SH IN-PROCESS

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1




samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
.100[2.54] C.I. SURFACE MOUNT SOCKET STRIP

DWG. NO.
SSM-1XX-XXX-XX-XX-XX-X-XX-XX

BY: KOLB 09/11/1998 SHEET 2 OF 4



SECTION "C"-"C"




FIG 4
-DH: DOUBLE HORIZONTAL
(SSM-1XX-XXX-DH-LC SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 3)





FIG 6
-P: PICK AND PLACE PAD
(SSM-110-XXX-SV-P SHOWN)
-02 AND -03 POS NOT AVAILABLE WITH POLARIZATION
-04 POS - CANNOT OFFER IF POLARIZATION IS POS 2 OR 3
-05 POS - CANNOT OFFER IF POLARIZATION IS POS 3
*MUST USE TR ON POS 2 & 3
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)
"R" = SEE FIG 1, SHEET 1 FOR OAL
"S" = IF NO OF POS IS EVEN: "R"/2 - .1975 [5.017]
IF NO OF POS IS ODD: "R"/2 - .2475 [6.287]




FIG 7
POLARIZATION
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

IF CENTER POS IS POLARIZED, USE TABLE BELOW

NO OF POS	DIRECTION PAD MOVED (1 POS TO NEXT AVAIL)	MIN POS	FORMULA
EVEN	LEFT	6	"S" = "R"/2 - .0975 [2.477]
EVEN	RIGHT	6	"S" = "R"/2 - .2975 [7.557]
ODD	LEFT	5	"S" = "R"/2 - .1475 [3.747]
ODD	RIGHT	7	"S" = "R"/2 - .3475 [8.827]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 3:2

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
.100 [2.54] C.L. SURFACE MOUNT SOCKET STRIP

DWG. NO.
SSM-1XX-XXX-XX-XX-XX-X-XX-XX

BY: KOLB 09/11/1998 SHEET 3 OF 4




FIG 8
-TR: TAPE AND REEL
SCALE 1:1







FIG 9
TUBE VIEWS



SSM-1XX-XXX-SV-LC-P SHOWN
(SSM-1XX-XXX-SV-LC-K SIMILAR)



SSM-1XX-XXX-SV-LC SHOWN

TABLE 2			
PART NUMBER	TUBE	PLUG	POS TO BE TUBED (SEE NOTE 4)
SSM-SV	PT-1-24-05-15	TP-24 (2)	03-36
SSM-SV-LC			02-36
SSM-SV-P	PT-1-24-02-15	TP-03 (2)	04-36
SSM-SV-K			03-36
SSM-SH	PT-1-24-07-15	TP-03 (2)	02-36
SSM-DH	PT-1-24-06-15	TP-07 (2)	02-36

• PROPRIETARY NOTE •

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 3:2

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
.100[2.54] C.L. SURFACE MOUNT SOCKET STRIP

DWG. NO.
SSM-1XX-XXX-XX-XX-XX-X-XX-XX

BY: KOLB 09/11/1998 SHEET 4 OF 4