





1. MATERIAL:
HOUSING (SEE TABLE) - COLOR: BLACK
TERMINAL - 0.36[.014] THICK PHOS BRONZE PLATED WITH 1.27 μ m [.000050] THICK HARD GOLD IN LOCALIZED GOLD PLATE AREA AND 3.81 μ m [.000150] THICK MATTE TIN IN SOLDER AREA OVER 1.27 μ m [.000050] THICK NICKEL UNDERPLATE
SHIELD - 0.25 [.010] THICK COPPER ALLOY PLATED WITH 3.0 μ m [.000120] MINIMUM THICK REFLOWED TIN
- 2 CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68, SUBPART F.
- 3 DIMENSIONS MEASURED ALONG FRONT EDGES OF MATING FACE

YES	HIGH TEMP NYLON	5555141-3
NO	PBT POLYESTER	5555141-1
IR PROCESS COMPATIBLE	HOUSING MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. GARRETT/L.A. MAYER CHK J. WESTMAN APVD S. FLICKINGER		04APR2005 04APR2005 04APR2005		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		MODULAR JACK ASSEMBLY,	
		0 PLC ± -		PRODUCT SPEC		SHIELDED, 8 POSITION, LOW PROFILE, RIGHT ANGLE,	
		1 PLC ± -		108-1163		PANEL GROUND WITH PANEL STOPS	
		2 PLC ± 0.13[.005]		APPLICATION SPEC			
		3 PLC ± -		114-2048			
		4 PLC ± -		WEIGHT -		SIZE CAGE CODE DRAWING NO	
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1		A1 00779		C=5555141	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1		REV B	