

D

C

B



A

D

C

B


A



SECTION B-B
SCALE 20:1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
		F	F1			APVD
CM	0			REVISED PER 0G3B-0237-05	9/21/05	SS
				REVISED PER ECR-14-000999	25JUL14	GK
						CJ
						KD

- 1 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
2. WIRE RANGE: 0.3 – 0.9MM² (22–18 AWG).
3. INSULATION RANGE: 1.50–2.79[.059–.110] DIA.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



SECTION A-A
SCALE 20:1

5	0.25[.010] BRASS	1-794229-0
1	0.25[.010] BRASS	794229-3
PRE-TIN	0.25[.010] BRASS	794229-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 1-15-97	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R. SWING 1-15-97				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± -		SOCKET, LOOSE PIECE,			
	1 PLC ± -		MINI UNIVERSAL MATE-N-LOK 2			
	2 PLC ± -		-			
	3 PLC ± 0.30 [.012]		SIZE			
	4 PLC ± -		CAGE CODE			
MATERIAL		FINISH	DRAWING NO		RESTRICTED TO	
SEE TABLE		SEE TABLE	A2 00779 C=794229		-	
CUSTOMER DRAWING			SCALE 10:1		SHEET 1 OF 1	
					REV F1	