


1.	MODEL:	35KM08			
2.	Dimension	Outer Diameter 16 X 35 mm.		Baffle Opening 15 X 32 mm.	
		Height	Refer to Drawing.	Weight	2.6 Grams.
3.	Magnet	Materials	Rare Earth	Size	ϕ 7.9 X 1.3 mm.
4.	Nominal Impedance	8 Ω	$\pm$ 15 %	At	1500 Hz.
5.	Power Rating	Normal	1000 mW.	Maximum	1500 mW.
6.	Lowest Resonant Frequency	650	$\pm$	20 %	Hz.
7.	Output Sound Pressure Lever (S.P.L.)	81	$\pm$ 3 db / 1.0 Watt	. 0.5 Meter.	
		Average at	800, 1000, 1200, 1500	Hz.	
8.	Frequency Range	400 ~ 20000	Hz.	Average S P L - 10 db.	
9.	Distortion	5 %	Maximum At	1000 Hz.	500 mW.
10.	Abnormal Sound Test	Must Be Normal Test By		2.83 Volts.	Sine Wave.
11.	Load Test	White Noise With Weighted Filter		2.83 Volts.(RMS)	24 Hrs.
12.	Polarity	Diaphragm shall move Forward when Apply a Positive DC.			
		Current to the "+" or "Marked" Terminal.			

MOUNTING NOTICE


AT LEAST
0.8mm
FOR
DIAPHRAM
MOVING



Unit : mm

Housing Material : ABS

35KMO8 UOL:2.828V(1.0W) DIS:0.5M VANSOONIC
X:1.0000kHz *Y:83.12dB ZA:2.0000 SSR Fund.



22-MAR-2001 10:16:41
Mode: SSR

