

Hanging scales KERN HDB-N · CH



KERN HDB-N



KERN CH



Convenient and always handy

Features

• Multi data hold function:

When the weighing value remains unchanged...

- the weight display is automatically „frozen“ for 5 sec

- the weight display is automatically „frozen“ until any key is pressed

By pressing the Hold key...

- the weight display can be „frozen“ for 5 sec

- the weight display can be „frozen“ until any key is pressed

HDB-N:

- **Hook (stainless steel)**, can be hinged
- **Ready for use:** Batteries included, 2 x 1.5 V AAA, operating time approx. 180 h, AUTO-OFF function to preserve the battery
- Further weighing units: kg, lb, N
- Permissible ambient temperature 5°C / 35°C

CH:

- **Hook (stainless steel)**
- **Tape measure**, extractable, length approx. 100 cm

- **Peak load display** (peak hold), measuring frequency 5 Hz
- **Ready for use:** 9V included, operating time approx. 20 h. AUTO-OFF function to preserve the battery, can be switched off
- Further weighing units: kg, lb, N
- Permissible ambient temperature 5°C / 35°C

STANDARD



STANDARD



OPTION



Model	Weighing range [Max] kg	Read-out [d] g	LCD display, digit height mm	Dimensions housing WxDxH mm	Height with hook mm	Net weight approx. kg	Option DKD Calibr. Certificate	
							DKD KERN	
KERN								
HDB 5K5N	5	5	12	70x25x105	195	0,15	963-127	
HDB 10K10N	10	10	12	70x25x105	195	0,15	963-128	
CH 15K20	15	20	11	90x30x175	270	0,25	963-128	
CH 50K50	50	50	11	90x30x175	270	0,25	963-128	
CH 50K100	50	100	11	90x30x175	270	0,25	963-128	

New model

KERN Pictograms



Internal adjusting (CAL): Quick setting of the balance's accuracy with internal adjusting weight (motordriven).



Adjusting program (CAL): For quick setting of the balance's accuracy. External adjusting weight required.



Weighing units: Can be switched to e.g. non-metric units at the touch of a key. See balance model. Please refer to KERN's website for more details.



Rechargeable battery pack: rechargeable set.



Power supply: integrated in balance. 230V/50Hz in Germany. On request GB, AUS or USA version.



Mains adapter: 230V/50Hz in standard version for Germany. On request GB, AUS or USA version.



Battery operation: The battery type is specified for each device.



Piece counting: Reference quantities selectable. Display can be switched from piece to weight



Spray and dust protection IPxx
The type of protection is shown by the pictogram. For details see the glossary.



Data interface: The type of interface is shown by the pictogram. See the glossary for further details.



GLP/ISO record keeping of weighing data with date, time and identification-no. Only with printers from KERN.



Tare: put back displayed value to "0" during weighing process, e.g. to add or remove weighing material from a container.



Dynamic weighing: Strong vibrations are filtered out to determine a stable weighing result.



Stainless steel: the balance is protected against corrosion.



Warranty: The warranty period is shown in the pictogram.



Net-total weighing: weight of tare cup and weight of components memorized in two separate stores.



Suspended weighing: load support with hook on the underside of the balance.



Verification possible: The time required for verification is specified in the pictogram.



Percentage determination: Determining the deviation in % from the target value (100%).



Weighing with tolerance range: Upper and lower limiting can be programmed individually, e.g. dosing/sorting.



DKD calibration possible: The time required for DKD calibration is specified in the pictogram.



Package shipment via courier.



Pallet shipment via freight forwarder.

[DMS] For details on weighing technologies, see the glossary.

Precision is our business

To ensure the high level of precision of your balance, KERN offers the appropriate test weight package for your balance. This consists of the test weight, box and DKD calibration certificate, as proof of its accuracy. The best way to ensure proper balance calibration.

In the extensive KERN test weight range, you will find test weights in the international OIML error limit classes: E1, E2, F1, F2, M1, M2, and M3 with weights from 1 mg to 2000 kg.

The KERN DKD calibration laboratory for electronic balances and weights has been accredited by DKD since 1994 and today is one of the most modern and best-equipped DKD calibration laboratories for balances, test weights and force-measurement in Europe.
(DKD = German Calibration Service)

Thanks to the high level of automation, we can carry out DKD calibration of balances, test weights and force-measuring devices 24 hours a day, 7 days a week.

Range of services:

- DKD calibration of balances with a maximum load of up to 6000 kg
- DKD calibration of weights in the range of 1 mg – 500 kg
- Database supported management of checking equipment and reminder service
- Calibration of force-measuring devices
- DKD calibration certificates in the following languages
D, GB, F, I, E, NL, PL

Do you have questions about your scale, the corresponding test weight or the calibration service? Your KERN specialist dealer will be pleased to assist you.

Your KERN specialist dealer:

KERN – Professional measuring. Measuring technology and testing services from a single source

