


PART NUMBER	C THREAD CLASS 2B	E DIA ±.005	K DIA MAX	R +.000 -.010	T THREAD CLASS 2A	RELEASE	MADE FROM
10-123011-6	.3125-32 UNEF	.190	.469	.215	.3750-32 UNEF	31508-287	10-123011- 6B
- 8	.4375-28 UNEF	.312	.594		.5000-28 UNEF		- 8B
-10	.5625-24 UNEF	.436	.719		.6250-24 UNEF		-10B
-12	.6875-24 UNEF	.561	.844		.7500-20 UNEF		-12B
-14	.8125-20 UNEF	.678	.969		.8750-20 UNEF		-14B
-16	.9375-20 UNEF	.802	1.094		1.0000-20 UNEF		-16B
-18	1.0625-18 UNEF	.894	1.219		1.1875-18 UNEF		-18B
-20	1.1875-18 UNEF	1.029	1.312	.312	1.1875-18 UNEF		-20B
-22	1.3125-18 UNEF	1.150	1.469		1.4375-18 UNEF		-22B
-24	1.4375-18 UNEF	1.274	1.594		1.4375-18 UNEF	33524-599	-24B

REL NO. 31508-287		REVISIONS		
CHG NO.	SYM	DESCRIPTION	DATE	APPROVED
43525-746	A1	REDRAWN, WAS SIZE "B" TYPE WRITTEN; PROVIDED ENVELOPE DWG	11-21-64 W. GAY	<i>W. Gay</i>
47524-170	A2	ADD & REL -XX9 FINISH	11-1-65 G. J. J.	<i>G. J. J.</i>
55524-58	A3	ADD & REL -XXG FINISH	11-1-67 DEMATTIO	<i>DEMATTIO</i>
72028-54	B	(CL II) ADD & REL -XX7 FINISH	5/12/81 WILKINSON	<i>WILKINSON</i>
76484-1	C	(CL II) ADDED MADE FROM COLUMN	10-2-81 J. J. J.	<i>J. J. J.</i>
80-44-1	D	(CL II) ADDED 9-1 SPEC TO NOTE 1	9-1-88 J. J. J.	<i>J. J. J.</i>
82906	E	(CL II) ADD & REL -XXY FINISH	3-5-97 J. J. J.	<i>J. J. J.</i>
85035	F	ADD AND RELEASE -XXY FINISH & DATA	10/1/93 J. J. J.	<i>J. J. J.</i>
85448	G	(CL II) SEE ECN: 85448	4-27-99 J. J. J.	<i>J. J. J.</i>
86546	H	(CL II) ADD & RELEASE -XXU FINISH & DATA	4-28-99 J. J. J.	<i>J. J. J.</i>



3. REF SYMBOL

2. THREADS ARE IN ACCORDANCE WITH FEDERAL HANDBOOK H-28.

1. TO COMPLETE PART NO., ADD APPLICABLE LAST DIGIT TO SUFFIX FOR DESIRED FINISH.

CHROMATE TREAT	SUFFIX - XX0
CADMIUM PLATE	SUFFIX - XX1
BLACK ANODIZE	SUFFIX - XX2
CADMIUM PLATE OLIVE DRAB	SUFFIX - XX3
GREY ANODIZE	SUFFIX - XX4
ANODIC COATING	SUFFIX - XX5
BRIGHT CADMIUM PLATE, NICKEL BASE	SUFFIX - XX7
NICKEL ALLOY PLATE	SUFFIX - XXG
CAD PLATE, O.D., NICKEL BASE	SUFFIX - XX9
BRIGHT NICKEL	SUFFIX - XX8
BLACK ZINC ALLOY PLATE	SUFFIX - XXY
BLACK ZINC CONDUCTIVE	SUFFIX - XXX

RELEASE NO.

38524-872	9-3350	GREEN ZINC
35524-218	9-2158	ALLOY PLATE
35524-218	9-3487	SUFFIX -XXU 9-9263
32525-260	9-3047	
31508-287	9-3487	
35508-72	9-3290	
55524-58	9-4332	
47524-170	9-6914	
42524-249	9-4960	
	9-3435	
	9-9181	
	9-9181-1	

USE OF THIS DOCUMENT IS UNLIMITED. DOCUMENTS REFERENCED HEREON CONTAIN LIMITED RIGHTS DATA.

ITEM NO.	QTY REQD	DESCRIPTION	PART NUMBER	CODE IDENT	ZONE
PARTS LIST					
UNLESS OTHERWISE SPECIFIED		DRAWN: HAYES DATE: 7-12-56			
LINEAR DIMENSIONS ARE IN INCHES.		CHECKED: Teelon DATE: 4-7-65			
TOLERANCES: 3 PLACES ±.010;		MATERIAL:			
2 PLACES ±.03; 1 PLACE ±.1;		STANDARDS: J. Balantieri 4-7-65			
ANGLES ±2°. OTHER STANDARDS PER SCINTILLA SPEC 9-3800 AND MIL-STD 8.		DRAFTING: D. Sweet 4-7-65			
MATERIAL SPEC ALUMINUM ALLOY		ENGINEERING: W. J. Harrison 4-7-65			
PROCESS SPEC		DEVELOPMENT:			
THE Bendix CORPORATION SCINTILLA DIVISION SIDNEY, NEW YORK, U.S.A.					
TITLE: ADAPTER, ELECTRICAL CONNECTOR, TYPE PB(), (ENVELOPE DRAWING)					
CODE IDENT NO.		SIZE		REF	
77820		C		10-123011	
SCALE NONE		WT		SHEET	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[10-123011-183](#) [10-123011-08G](#) [10-123011-18G](#) [10-123011-20G](#) [10-123011-081](#) [10-123011-083](#) [10-123011-103](#)
[10-123011-105](#) [10-123011-10G](#) [10-123011-123](#) [10-123011-125](#) [10-123011-12G](#) [10-123011-143](#) [10-123011-14G](#)
[10-123011-163](#) [10-123011-16G](#) [10-123011-203](#) [10-123011-223](#) [10-123011-22G](#) [10-123011-145](#) [10-123011-16Y](#)
[10-123011-122](#) [10-123011-165](#) [10-123011-085](#) [10-123011-243](#) [10-123011-20X](#) [10-123011-10X](#) [10-123011-185](#) [10-](#)
[123011-225](#) [10-123011-20Y](#) [10-123011-141](#) [10-123011-181](#) [10-123011-16X](#) [10-123011-12X](#) [10-123011-12Y](#) [10-](#)
[123011-08X](#) [10-123011-14X](#) [10-123011-18X](#) [10-123011-22X](#) [10-123011-14Y](#) [10-123011-10Y](#) [10-123011-121](#)