





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		D	REVISED PER ECR-14-016452	05DEC2014	NK	DH

1 CONTINUOUS STRIP ON REELS.


△2 NICKEL 0.00381[.000150] MIN THICK.



VIEW A-A
SCALE 8:1




SECTION B-B
SCALE 8:1



SECTION C-C
SCALE 8:1

2.79-5.08 [.110-.200]	[#18-#14] OR TWO [#18'S]	0.813±0.025 [.032±.001]	63963-1
INSUL RANGE	WIRE SIZE	MATING TAB THICKNESS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 6/10/97	 TE Connectivity					
		CHK MS FEHER 6/10/97						
DIMENSIONS: mm[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD P DESANTIS 6/10/97	NAME RECPT, FASTON, FLAG, .250 SERIES					
	0 PLC ± -	PRODUCT SPEC						
	1 PLC ± -	—						
	2 PLC ± -	APPLICATION SPEC						
	3 PLC ± 0.25 [.010]	114-2079	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
	4 PLC ± -	WEIGHT	A3	00779	C-63963			
MATERIAL H02 STEEL	FINISH NICKEL 	CUSTOMER DRAWING				SCALE	SHEET	REV
						5:1	1 OF 1	D