





PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24A.PL00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24A.PL00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24A.PL00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24A.PL00LF

Plating: 4 --> flash AU
Plating: 6 --> 0.76μ AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

Notes:

1) The nut can protrude above the surface of insulator but maintaining the footprint dimension 6.0±0.15 mm.

mat'l. code —				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D-SUB				
ltr	ecn no	dr	date	tolerances unless otherwise specified						MM 	title			
E	ELX-I-21256	AB	2015/07/14	angles	linear	.0±.0.1					FEMALE CONNECTOR DELTA-D			
						.00±0.1					STRAIGHT - SOLDER TYPE FOR 1.6mm			
				0°±2'		.000±0.1					scale 2:1			
				dr	JOUBERT		1996/09/10			dwg no		sheet 1 of 1		size
				engr	ALIAS BABU		2015/07/14			C01-8646-0491		A3		
				chr	MITHUN PAUL		2015/07/14							
				app	BIJU K PAUL		2015/07/14			type Product Customer Drawing				
sheet index		revision sheet		E	1									