

FUSE HOLDER SELECTION GUIDE

Fuse Type	Fuse Series	Panel Mount	PC Board	Blocks	Clips	In- Line
4.5x14.5 mm (2AG)	225	3452 International Shock-Safe	254101	254 Omni-Blok	111501	150274
	229	345 International shock-Safe (old)	254121 Beryllium Copper		111505 Beryllium Copper	
		245001 Shorty Solder QC			111506	
		245002 Shorty NEMA QC				
5x20 mm		286377 Flip Top				
	213	3455 International Shock-Safe	345121 horizontal	520003 Omni-Blok QC	111501	150274
	215	345 International shock-Safe (old)	521101 Omni-Blok	520004 Omni-Blok Soder	445001	
	216	286377 Flip Top	OPTF0060W no cover optional	520005 Omni-Blok anti-rotation	111505 Beryllium Copper	
	217	800	OPTF0075P cover optional		30210	
	218	820	OOPS0232P cover		111506 Beryllium Copper	
	219A	823 snap-in	646		520001	
	232	821	648 cover	FB58A	100054	
	233	850	640 cover and puller combo	FB58B	100056	
	234	851	649		111005 T&R	
	235	860 4 Watt	656 659,660 cover		519 T&R	
	239	870 medical,captive cap	658 Surface Mt 659,660 cover		520	
		FH503R	810 horizontal		521	
		FH503S	830 horizontal		518 Combo,3AA & 5X20	
			862 horizontal			
			811 vertical			
6.3x32 mm (3AB/3AG)	312	34453 International Shock-Safe	345101 horizontal	354 Omni-Blok	102071	155100 Twist-Lock
	313	345 International shock-Safe (old)	810 horizontal	356 Screw terminal	102074	150215 Assem,no Fuse
	314	342 Traditional	862 horizontal	359 Screw terminal	122083	155000 Heavy Duty
	326	344 Indicating Snap Mount	811 vertical	FB66A	122067 Beryllium Copper	150079 Assem,no Fuse
		348 Snap Mount			122088 Beryllium Copper	150322 120VAC UL
		346377 Flip Top			122093 Beryllium Copper	
		342006 Watertight screw-in			102078	
		340312/3 Shielded Watertight			102079	
		342024 MII high temp knurled			102076	
		342025 MII high temp fluted			102076	
		800 2.5 Watt			102080	
		80001 500V 2.5 Watt			122090 Beryllium Copper	
		860 4 Watt			121001 Beryllium Copper	
		FH602R			100058	
		FH604R			101001	
TE5®/TR5®	370,372	570	559			
	373,378	575 cap	560			
	374,379		562			
	375,382		564			
Micro™/TR3®			565 90°			
			571			
			575 cap			
	272 273	282001 Front mt.Neoprene	281005 Vertical silver			
	262 268	282007 Front mt.Conductive	281007 Horizontal silver			
	269 24	282002 Rear mt Neoprene	281008 Vertical tin			
	279	282008 Rear mt.Conductive	281010 Horizontal tin			
		280003 125V indicating				
		280004 32V indicating				

4.5mm x 14.5mm (2AG) SIZE FUSE SERIES AND HOLDER OPTIONS



Fuse Series Name	Time Lag (Slo-Blo) ⁹	Medium Acting	Fast Acting	Very Fast Acting	Device Range ³ (Operating Current Options in Amps)	Max. Voltage Rating ³ (Volts)	Interrupting Rating at Max Voltage Rating ³ (Amps)	Operating Temperature Range	Agency Approvals ³												RoHS Compliant	Lead Free	
									Americas				Europe				Asia						
									UL	UR	CSA	QPL	CE	VDE	TUV	BSI	Semko	PSE	K	CCC			CQC
208			•		0.125 - 10	350	100	-55°C to +125°C			•						•				•	•	
209	•				0.25 - 1	350	100				•							•				•	•
224/225			•		0.1 - 10	250 / 125	35 - 500		•	•	•							•				•	•
229/230	•				0.25 - 7	250 / 125	35 - 400		•	•	•							•				•	•

Panel Mount Holders	PC Board Mount Holders	Blocks	Clips	In-Line Holders
3452 International Shock-Safe 345 International shock-Safe (old) 245001 Shorty Solder QC 245002 Shorty NEMA QC 286377 Flip Top	254101 254121 Beryllium Copper	254 Omni-Blok	111501 111505 Beryllium Copper 111506	150274

5mm x 20mm SIZE FUSE SERIES AND HOLDER OPTIONS



Series Name ¹	Time Lag (Slo-Blo®)	Medium Acting	Fast Acting	Very Fast Acting	Device Range ³ (Operating Current Options in Amps)	Max. Voltage Rating ³ (Volts)	Interrupting Rating at Max Voltage Rating ³ (Amps)	Operating Temperature Range	Agency Approvals ³												RoHS Compliant	Lead Free	
									Americas				Europe				Asia						
									UL	UR	CSA	OPL	CE	VDE	TUV	BSI	Semko	PSE	K	CCC			COC
217			•		0.032 - 15	250	35 - 150	-55°C to +125°C		•	•		•	•		•	•	•	•	•		•	•
218	•				0.032 - 16	250	35 - 100			•	•		•	•		•	•	•	•	•		•	•
213	•				0.2 - 6.3	250	35 - 63			•	•		•	•			•					•	•
219XA	•				0.4 - 6.3	250	150			•	•		•	•			•					•	•
216			•		0.05 - 16	250	750 - 1500			•	•		•	•		•	•	•	•			•	•
215	•				0.125 - 25	250	300 - 1500			•	•		•	•		•	•	•	•			•	•
232		•			1 - 10	250 / 125	300 / 10,000				•					•	•					•	•
235			•		0.1 - 7	250 / 125	35 - 10,000			•		•				•	•					•	•
233		•			1 - 10	125	10,000			•		•				•	•					•	•
234		•			1 - 10	250	100 - 200			•		•				•	•					•	•
239	•				0.08 - 7	250 / 125	35 - 10,000			•		•				•	•					•	•
477	•				0.5 - 16	400DC / 500AC	100 - 1500				•					•	•	•				•	•

Panel Mount Holders	PC Board Mount Holders	Blocks	Clips	In-Line Holders
3455 International Shock-Safe 345 International shock-Safe (old) 286377 Flip Top 800 820 823 snap-in 821 850 851 860 4 Watt 870 medical,captive cap FH503R FH503S	345121 horizontal 521101 Omni-Blok OPTF0060W no cover optional OPTF0075P cover optional OOPS0232P cover 646 648 cover 640 cover and puller combo 649 656 659,660 cover 658 Surface Mt 659,660 cover 810 horizontal 830 horizontal 862 horizontal 811 vertical 831 vertical 4pin 834 vertical 852 vertical 2 pin 853 vertical 2pin 860 4 Watt	520003 Omni-Blok QC 520004 Omni-Blok Soder 520005 Omni-Blok anti-rotation FB58A FB58B	111501 445001 111505 Beryllium Copper 30210 111506 Beryllium Copper 520001 100054 100056 111005 T&R 519 T&R 520 521 518 Combo,3AA & 5X20	150274

6.3mm x 32mm (3AB / 3AG) SIZE FUSE SERIES AND HOLDER OPTIONS



Series Name ¹	Time Lag (Slo-Blo [®])	Medium Acting	Fast Acting	Very Fast Acting	Device Range ³ (Operating Current Options in Amps)	Max. Voltage Rating ³ (Volts)	Interrupting Rating at Max Voltage Rating ³ (Amps)	Operating Temperature Range	Agency Approvals ³												RoHS Compliant	Lead Free	
									Americas				Europe				Asia						
									UL	UR	CSA	OPL	CE	VDE	TUV	BSI	Semko	PSE	K	CCC			CQC
312/318			•		0.01 - 35	250 / 125 / 32	35 - 300	-55°C to +125°C	•	•	•		•					•	•			•	•
313/315	•				0.01 - 30	250 / 125 / 32	35 - 300		•	•	•		•					•	•			•	•
314/324			•		0.125 - 40	250	35 - 1000		•	•	•		•					•	•			•	•
322				•	1 - 30	250 / 65	100 - 1000			•			•					•				•	•
325/326	•				0.01 - 30	250 / 125	100 - 600		•	•	•		•					•	•			•	•
388			•		1 - 30	250	100						•					•	•			•	•
505			•		10 - 30	450 / 500	20,000 - 50,000			•			•									•	•

Panel Mount Holders	PC Board Mount Holders	Blocks	Clips	In-Line Holders
34453 International Shock-Safe	345101 horizontal	354 Omni-Blok	102071	155100 Twist-Lock
345 International shock-Safe (old)	810 horizontal	356 Screw terminal	102074	150215 Assem,no Fuse
342 Traditional	862 horizontal	359 Screw terminal	122083	155000 Heavy Duty
344 Indicating Snap Mount	811 vertical	FB66A	122067 Beryllium Copper	150079 Assem,no Fuse
348 Snap Mount			122088	150322 120VAC UL,
346377 Flip Top			122093 Beryllium Copper	
342006 Watertight screw-in			102078	
340312/3 Shielded Watertight			102079	
342024 MII high temp knurled			102076	
342025 MII high temp fluted			102076	
800 2.5 Watt			102080	
80001 500V 2.5 Watt			122090 Beryllium Copper	
860 4 Watt			121001 Beryllium Copper	
FH602R			100058	
FH604R			101001	
			101002	
			101003	
			102064	
			121004 Beryllium Copper	
			121002 Beryllium Copper	
			518 Combo,3AA & 5X20	

FUSE HOLDER RE-RATING:

For 25°C ambient temperatures, it is recommended that fuse holders be operated at no more than 60% of the nominal current rating established using the controlled test conditions specified by Underwriters Laboratories.

The primary objective of these UL test conditions is to specify common test standards necessary for the continued control of manufactured items intended for protection against fire, etc. A copper dummy fuse is inserted in the fuse holder by Underwriters Laboratories, and then the current is increased until a certain temperature rise occurs.

The majority of the heat is produced by the contact resistance of the fuse holder clips. This value of current is considered to be the rated current of the fuse holder, expressed as 100% of rating.

Some of the more common, everyday applications may differ from these UL test conditions as follows: fully enclosed fuse holders, high contact resistance, air movement, transient spikes, and changes in connecting cable size (diameter and length).

Even small variations from the controlled test conditions can greatly affect the ratings of the fuse holder. For this reason, **it is recommended that fuse holders be de-rated by 40% (operated at no more than 60% of the nominal current rating established using the Underwriter Laboratories test conditions).**

TE5®/TR5® TYPE FUSE SERIES AND HOLDER OPTIONS



Series Name ¹	Time Lag (Slow-Blo [®])	Medium Acting	Fast Acting	Very Fast Acting	Device Range ³ (Operating Current Options in Amps)	Max. Voltage Rating ³ (Volts)	Interrupting Rating at Max Voltage Rating ³ (Amps)	Operating Temperature Range	Agency Approvals ³												RoHS Compliant	Lead Free		
									Americas				Europe				Asia							
									UL	UR	CSA	QPL	CE	VDE	TUV	BSI	Semko	PSE	K	CCC			CQC	
370			•		0.4 - 6.3	250	35 - 50	-40°C to +85°C		•				•			•	•		•	•	•	•	
372	•				0.4 - 6.3	250	35 - 50			•				•			•	•	•	•	•	•	•	
373			•		0.5 - 10	250	50		•		•												•	•
374	•				0.5 - 10	250	50		•		•												•	•
382	•				1 - 10	250	100			•				•			•	•	•	•	•	•	•	•
383	•				1 - 10	300	50 - 100			•				•			•						•	•
369	•				1 - 6.3	300	50	-40°C to +85°C		•							•					•	•	
385	•				0.35 - 1.5	125	50			•												•	•	
391			•		0.125 - 4	65	50			•												•	•	
392	•				0.8 - 6.3	250	25 - 63			•				•			•	•	•		•	•	•	•
395			•		0.05 - 6.3	125	100		•									•					•	
396	•				0.05 - 6.3	125	100		•									•					•	•
397	•				0.35 - 1.5	125	50		•														•	•
398		•			0.125 - 4	65	50			•													•	•
399	•				0.125 - 4	65	50			•													•	•
400	•				0.5 - 6.3	250	130			•				•			•						•	•

Panel Mount Holders	PC Board Mount Holders
570	559
575 cap	560
	562
	564
	565 90°
	571
	575 cap

MICRO™/TR3® TYPE FUSE SERIES AND HOLDER OPTIONS



Series Name ¹	Time Lag (Slow-Blo®)	Medium Acting	Fast Acting	Very Fast Acting	Device Range ³ (Operating Current Options in Amps)	Max. Voltage Rating ³ (Volts)	Interrupting Rating at Max Voltage Rating ³ (Amps)	Operating Temperature Range	Agency Approvals ³												RoHS Compliant	Lead Free	
									Americas				Europe				Asia						
									UL	UR	CSA	QPL	CE	VDE	TUV	BSI	Semko	PSE	K	CCC			COC
262/268/269				•	0.002 - 5	125	10,000	-55°C to +125°C		•	•	•											
272/278				•	0.002 - 5	125	10,000	-55°C to +125°C		•	•	•											
273/274/279				•	0.002 - 5	125	10,000	-55°C to +85°C															
303		•			0.5 - 5	125	50	-55°C to +70°C	•		•											•	•

Panel Mount Holders	PC Board Mount Holders
282001 Front mt.Neoprene	281005 Vertical silver
282007 Front mt.Conductive	281007 Horizontal silver
282002 Rear mt Neoprene	281008 Vertical tin
282008 Rear mt.Conductive	281010 Horizontal tin
280003 125V indicating	
280004 32V indicating	