


| DCP # | REV | DESCRIPTION | DRAWN | DATE | CHECKD | DATE | APPRVD | DATE |
|-------|-----|------------------------------|-------|----------|--------|----------|--------|---------|
| 370 | B | Type Nos 3628 and 3627 added | JWM | 12/11/97 | J.C. | 12/18/97 | | |
| 1779 | C | RoHS ADDED | DCM | 1/24/06 | JWM | 1/24/06 | JWM | 1/24/06 |



| SPC Type No. | Thread Size | "L" | "B" Minimum |
|--------------|-------------|---------------|-------------|
| 2436 | 4-40 | 1/4 [6.35] | 3/16 [4.76] |
| 2437 | 4-40 | 3/8 [9.53] | |
| 2438 | 4-40 | 1/2 [12.70] | |
| 2439 | 4-40 | 5/8 [15.88] | |
| 2440 | 4-40 | 3/4 [19.05] | |
| 2441 | 4-40 | 7/8 [22.22] | |
| 2442 | 4-40 | 1 [25.40] | |
| 3628 | 4-40 | 1 3/8 [34.93] | |
| 3627 | 4-40 | 2 [50.80] | 1/4 [6.35] |
| 2443 | 6/32 | 1/4 [6.35] | |
| 2444 | 6/32 | 3/8 [9.53] | |
| 2445 | 6/32 | 1/2 [12.70] | |
| 2446 | 6/32 | 5/8 [15.88] | |
| 2447 | 6/32 | 3/4 [19.05] | |
| 2448 | 6/32 | 7/8 [22.22] | |
| 2449 | 6/32 | 1 [25.40] | |
| 2450 | 8-32 | 1/4 [6.35] | 3/8 [9.53] |
| 2451 | 8-32 | 3/8 [9.53] | |
| 2452 | 8-32 | 1/2 [12.70] | |
| 2453 | 8-32 | 5/8 [15.88] | |
| 2454 | 8-32 | 3/4 [19.05] | |
| 2455 | 8-32 | 7/8 [22.22] | |
| 2456 | 8-32 | 1 [25.40] | |

SPC-F004.DWG

| | | | | | | |
|--|---------------|----------|--------------------------------------|----------|---------------------|---------------|
| TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY. | DRAWN BY: | DATE: | DRAWING TITLE: | | | |
| | Jeff McVicker | 9/24/97 | Male/Female Nylon Threaded Standoffs | | | |
| | CHECKED BY: | DATE: | SIZE | DWG. NO. | ELECTRONIC FILE | REV |
| | JOHN COLE | 10/10/97 | A | TA-126 | ta-126.dwg | C |
| | APPROVED BY: | DATE: | SCALE: NTS | | U.O.M.: INCHES [mm] | SHEET: 1 OF 1 |
| | BRETT BRAATZ | 10/14/97 | | | | |