



PART NUMBER
10120045-40ILF



SCALE 2.000




SCALE 3.000



www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		MM 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M JACOB	2014-05-12	ANGULAR	LINEAR	0.X ±X		size A4	Scale 1.000		
Eng	M JACOB	2014-05-12			0.XX ±0.2					
Chr	M JACOB	2014-05-12			0.XXX ±X					
Appr	BIJU K PAUL	2014-05-12	0° ±2°		ECN ELX-1-22313					
			Product family - RotaConnect					Spec ref -		
			title ASSEMBLY, 4 POS HOR TYPE WITH PEG ROTATABLE BOARD TO BOARD CONNECTOR				dwg no 10120045-40IC		Rev. B	
			catalog no 10120045-40ILF				CUSTOMER DRAWING		sheet 2 of 2	

rev	ecn no	dr	date
B	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-


PART NUMBER
10120045-401LF



SECTION A-A



Component inside carrier tape




DETAIL D
SCALE 2:1

NOTES :

1. MATERIAL : ANTI-STATIC POLYSTYRENE
2. PACKAGING AS PER EIA-481 STD.
3. QTY PER REEL : 710 NOS

rev	ecn no	dr	date
B	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		MM 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M JACOB	2014-05-12	ANGULAR	LINEAR	0.X	±X	size A4	Scale 1.000		
Eng	M JACOB	2014-05-12			0.XX	± 0.2				
Chr	M JACOB	2014-05-12	0°	±2°	0.XXX	±X	ECN		ELX-I-22313	
Appr	BIJU K PAUL	2014-05-12	Product family- RotaConnect					Spec ref -		
		title	ASSEMBLY, 4 POS HDR TYPE WITH PEG ROTATABLE BOARD TO BOARD CONNECTOR				dwg no	10120045-401C		Rev B
		catalog no :	10120045-401LF			CUSTOMER DRAWING		sheet 3 of 3		