




10

9

8

7

6



5

4



3

2



1



2~3 極形状 (ロック面及び反ロック面)



4~5 極形状 (ロック面及び反ロック面)




6~7 極形状 (ロック面及び反ロック面)

FIGURE OF 2-3 CIRCUIT (LOOK SIDE AND UN-LOCK SIDE)


FIGURE OF 4-5 CIRCUIT (LOOK SIDE AND UN-LOCK SIDE)

FIGURE OF 6-7 CIRCUIT (LOOK SIDE AND UN-LOCK SIDE)




8~10 極形状 (反ロック面)

FIGURE OF 8-10 CIRCUIT (UN-LOCK SIDE)



11~15 極形状 (反ロック面)

FIGURE OF 11-15 CIRCUIT (UN-LOCK SIDE)



基板取付穴推奨寸法 (マウント面)

RECOMMENDED P.C.BOARD
HOLE DIMENSION
(MOUNTING SIDE)
($t=1.6$)REVISED
EC NO: J2014-1798
DRWN:TYAJIMA01 2014/06/10
CHKD:KASAKAWA 2014/06/11
APPR:NUKITA 2014/06/12
J

DESCRIPTION

GENERAL TOLERANCES
(UNLESS SPECIFIED)10 UNDER ± 0.2 10 OVER 30 UNDER ± 0.25 30 OVER ± 0.3 ANGULAR $\pm 3^\circ$ DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE

MM ONLY

DRAWN BY

DATE

CHECKED BY

DATE

KASAKAWA

2008/06/06

APPROVED BY

DATE

SICHIKAWA

2008/06/06

MATERIAL NO.

SEE TABLE

SIZE

A3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE

4:1

DESIGN UNITS

METRIC

THIRD ANGLE
PROJECTION

TITLE

1.5 W/B CONN. SINGLE DIP
ST REC. ASS'Y 2-15CKT

molex

DOCUMENT NO.

SD-503159-001

SHEET NO.

2 OF 3

F

E

D

C

B

A

F

E

D

C

B

A

NOTES

1. 嵌合相手: 502578 シリーズ
MATE WITH : 502578 SERIES.
- △ 極数/2=偶数に適用
APPLY FOR CIRCUIT SIZE/2=EVEN.
3. 端子テール部に錫めっきを使用している為、外観に摺動痕が付く場合があります。
THE WOUND OF FRICTION MIGHT ADHERE TO EXTERNALS
BECAUSE THE TIN PLATING IS USED FOR THE TAIL.
4. 製品番号
MATERIAL No.
503159-***
- 極数
CIRCUIT SIZE

ボス、色
BOSS, COLOR
- ボス有り

CIRCUIT	No.	COLOR
02~15	0	0 ベージュ BEIGE
		1 黒 BLACK
		2 赤 RED
		3 黄 YELLOW
		4 青 BLUE
		5 桃 PINK
		6 緑 GREEN
		7 茶 BROWN
		8 橙 ORANGE
9 紫 VIOLET		
02~05	2	1 灰 GRAY
		4 水 PALE BLUE
		6 黄緑 YELLOWISH GREEN
02	2	3 蛍光黄 FLUORESCENCE YELLOW
5. 本製品のプラスチック部に黒点・白点等が確認される場合や色合いが異なる場合がありますが、製品性能に影響はありません。
THERE IS NO INFLUENCE IN THE PRODUCT PERFORMANCE THOUGH THE BLACK AND WHITE SPOT ETC. MIGHT BE CONFIRMED TO THE PLASTIC PART OF THIS PRODUCT AND THE SHADE MIGHT BE DIFFERENT.
6. ELV及びRoHS適合品
ELV AND RoHS COMPLIANT
- △ トレードマーク: Mプラス1~2文字のアルファベットにて構成 (例 MXJ)
但し "J" はJAPANを示す。
キャビティー番号: 1桁~2桁の数字で構成。
金型番号: アルファベット1文字にて構成。
TRADE MARK: FORMED BY M AND 1~2 MORE LETTER OF ALPHABET (e.g. MXJ), BUT "J" MEANS JAPAN.
CAVITY NO.: FORMED BY 1 DIGIT TO 2 DIGIT NUMBERS.
MOLD NO.: FORMED BY 1 LETTER OF ALPHABET.

REVISED EC NO: J2014-1798 DRWN: TYAJIMA01 2014/06/10 CHKD: KASAKAWA 2014/06/11 APPR: NUKITA 2014/06/12 J	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY TYAJIMA01	DATE 2014/06/10	TITLE 1.5 W/B CONN. SINGLE DIP ST REC. ASS'Y 2-15CKT				
		10 OVER 30 UNDER	± 0.25	CHECKED BY KASAKAWA	DATE 2014/06/11					
		30 OVER	± 0.3	APPROVED BY NUKITA	DATE 2014/06/12					
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO. SD-503159-001				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE								
		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							