


22787879
THIS DRAWING IS A CONTROLLED DOCUMENT

Restricted to: General Release

USED ON




Left Side

Connector(s): MT-RJ SECURE (No Pins)

Mode: MM

Housing Color: Blue

Geom. Spec: 115-1215



VIEW C-C
NOT TO SCALE

Fiber Path

Fiber A -  - Fiber B
Fiber B -  - Fiber A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Label 2 will not be present on any cable assembly less than 5 meters long.
- 3 Includes dust caps (not shown on print).


Right Side

Connector(s): MT-RJ (No Pins)

Mode: MM

Housing Color: Black

Geom. Spec: 115-1215



VIEW D-D
NOT TO SCALE

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	B	Rev Per EC#	06-020853	8/30/2006	-	MK			
P	LTR	REVISION	RECORD	DATE	DN	APVD			

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Customer Print

DIN	Cable Assy Configurator	MATERIAL	HEAT TREAT
CHK	Michael Kepko		
APVD	Michael Kepko		
NAME	FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to MT-RJ (No Pins)		
SCALE	NTS	SIZE	A2
DRAWING NO	C- 6278876	SHEET	1 of 3
REV	B		

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

THIS DRAWING IS A CONTROLLED DOCUMENT.

Restricted to: General Release

USED ON

Part #	L (meters)	L (feet)	MT-RJ SECURE (No Pins), Blue		MT-RJ (No Pins), Black	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-6278876-1	0.950 - 1.050	3.11 - 3.44	0.5	20	0.5	20
0-6278876-2	1.950 - 2.050	6.39 - 6.72	0.5	20	0.5	20
0-6278876-3	2.950 - 3.050	9.67 - 10.00	0.5	20	0.5	20
0-6278876-4	3.920 - 4.080	12.86 - 13.38	0.51	20	0.51	20
0-6278876-5	4.920 - 5.080	16.14 - 16.66	0.51	20	0.51	20
0-6278876-6	5.920 - 6.080	19.42 - 19.94	0.51	20	0.51	20
0-6278876-7	6.920 - 7.080	22.70 - 23.22	0.51	20	0.51	20
0-6278876-8	7.920 - 8.080	25.98 - 26.50	0.51	20	0.51	20
0-6278876-9	8.850 - 9.150	29.03 - 30.01	0.51	20	0.51	20
1-6278876-0	9.850 - 10.150	32.31 - 33.30	0.52	20	0.52	20
1-6278876-1	10.850 - 11.150	35.59 - 36.58	0.52	20	0.52	20
1-6278876-2	11.850 - 12.150	38.87 - 39.86	0.52	20	0.52	20
1-6278876-3	12.850 - 13.150	42.15 - 43.14	0.52	20	0.52	20
1-6278876-4	13.850 - 14.150	45.43 - 46.42	0.52	20	0.52	20
1-6278876-5	14.850 - 15.150	48.72 - 49.70	0.52	20	0.52	20
1-6278876-6	15.840 - 16.160	51.96 - 53.01	0.52	20	0.52	20
1-6278876-7	16.830 - 17.170	55.21 - 56.33	0.53	20	0.53	20
1-6278876-8	17.820 - 18.180	58.46 - 59.64	0.53	20	0.53	20
1-6278876-9	18.810 - 19.190	61.71 - 62.95	0.53	20	0.53	20
2-6278876-0	19.800 - 20.200	64.96 - 66.27	0.53	20	0.53	20
2-6278876-1	20.790 - 21.210	68.20 - 69.58	0.53	20	0.53	20
2-6278876-2	21.780 - 22.220	71.45 - 72.90	0.53	20	0.53	20
2-6278876-3	22.770 - 23.230	74.70 - 76.21	0.53	20	0.53	20
2-6278876-4	23.760 - 24.240	77.95 - 79.52	0.54	20	0.54	20
2-6278876-5	24.750 - 25.250	81.20 - 82.84	0.54	20	0.54	20
2-6278876-6	25.740 - 26.260	84.44 - 86.15	0.54	20	0.54	20
2-6278876-7	26.730 - 27.270	87.69 - 89.46	0.54	20	0.54	20
2-6278876-8	27.720 - 28.280	90.94 - 92.78	0.54	20	0.54	20
2-6278876-9	28.710 - 29.290	94.19 - 96.09	0.54	20	0.54	20
3-6278876-0	29.700 - 30.300	97.44 - 99.40	0.55	20	0.55	20
3-6278876-1	30.690 - 31.310	100.68 - 102.72	0.55	20	0.55	20
3-6278876-2	31.680 - 32.320	103.93 - 106.03	0.55	20	0.55	20
3-6278876-3	32.670 - 33.330	107.18 - 109.35	0.55	20	0.55	20
3-6278876-4	33.660 - 34.340	110.43 - 112.66	0.55	20	0.55	20
3-6278876-5	34.650 - 35.350	113.68 - 115.97	0.55	20	0.55	20
3-6278876-6	35.640 - 36.360	116.92 - 119.29	0.55	20	0.55	20
3-6278876-7	36.630 - 37.370	120.17 - 122.60	0.56	20	0.56	20
3-6278876-8	37.620 - 38.380	123.42 - 125.91	0.56	20	0.56	20
3-6278876-9	38.610 - 39.390	126.67 - 129.23	0.56	20	0.56	20
4-6278876-0	39.600 - 40.400	129.92 - 132.54	0.56	20	0.56	20
5-6278876-0	49.500 - 50.500	162.40 - 165.68	0.58	20	0.58	20

Qty	U of M	Description	Item No.
1	piece	HOUSING, CONN, MT-RJ.BLACK	1
2	piece	DUST COVER, MT-RJ	2
2	piece	SPRING, MT-RJ, 3.8 DESIGN	3
2	piece	PIN KEEPER, 3.8MM	4
2	piece	MT-RJ, SPRING PUSH, UNIVERSAL	5
2	piece	CRIMP EYELET, MT-RJ	6
1	piece	MT-RJ Keyed Connector Housing - Blue	7
2	piece	MT-RJ FERRULE, THERMOPLAST,MM	8
AR	meter	2 fiber, 50/125, 1.8 mm, Twinzip, Orange, OFNR (Riser)	9
2	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	10
2	piece	Trace Label	11

	B	Rev Per EC#	06-020853	8/30/2006	-	MK	
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Customer Print

DIN Cable Assy Configurator

OK Michael Kepko

APVD Michael Kepko

MATERIAL -

HEAT TREAT -

Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

NAME FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, MT-RJ SECURE
(No Pins) to MT-RJ (No Pins)

SCALE NTS

SIZE A2

DRAWING NO C- 6278876

SHEET 2 of 3

REV B

8 7 6 5 4 3 2 1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

1